



# Product Description

## Appliance Oven Tubular

Tubular vacuum lamps with clear glass (T-bulb)

### Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

### Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

### Application

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight



### Versions



E14, T25, Clear

# Appliance Oven Tubular

## Dimensional drawing



Product	D (max)	C (max)
Appliance 15W E14 230-240V T22 CL OV 1CT	22 mm	49 mm

Product	D (max)	C (max)
Appliance 25W E14 230-240V T25 CL OV 1CT	25 mm	57 mm
Appliance 25W E14 230-240V T25 CL OV 1CT		

### Approval and Application

Energy Efficiency Label (EEL) E

### Controls and Dimming

Dimmable Yes

### Operating and Electrical

Voltage (Nom) 230-240 V

Starting Time (Nom) 0.0 s

Warm Up Time To 60% Light (Nom) instant full light

### General Information

Cap-Base E14

Nominal Lifetime (Nom) 1000 h

Main Application Oven

Operating Position UNIVERSAL

Rated Lifetime (Hours) 1000 h

Switching Cycle 4000X

### Light Technical

Correlated Color Temperature (Nom) 2700 K

Color Rendering Index (Nom) 100

### Mechanical and Housing

Bulb Finish Clear

### Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
94703800	Appliance 15W E14 230-240V T22 CL OV 1CT	15 kWh
94712000	Appliance 25W E14 230-240V T25 CL OV 1CT	25 kWh
03871550	APP 25W E14 230-240V T25 CL OV 1CT	25 kWh

## Operating and Electrical

## Appliance Oven Tubular

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
94703800	Appliance 15W E14 230-240V T22 CL OV 1CT	0.06 A	15.0 W
94712000	Appliance 25W E14 230-240V T25 CL OV 1CT	0.11 A	25.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
03871550	APP 25W E14 230-240V T25 CL OV 1CT	0.11 A	25.0 W

### Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
94703800	Appliance 15W E14 230-240V T22 CL OV 1CT	90 lm	90 lm
94712000	Appliance 25W E14 230-240V T25 CL OV 1CT	172 lm	172 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
03871550	APP 25W E14 230-240V T25 CL OV 1CT	172 lm	172 lm

### Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
94703800	Appliance 15W E14 230-240V T22 CL OV 1CT	T22
94712000	Appliance 25W E14 230-240V T25 CL OV 1CT	T25

Order Code	Full Product Name	Bulb Shape
03871550	APP 25W E14 230-240V T25 CL OV 1CT	T25

