



OptiVision – breakthrough downlight

OptiVision MVP507

OptiVision is an asymmetric downlighting luminaire that combines compact dimensions with very high efficiency. Available with narrow, medium and wide beams for flexibility in application, it provides excellent control of spill light and limitation of glare and upward leakage of light. OptiVision can accommodate metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Excellent spill-light control, limitation of glare and upward leakage of light is secured by asymmetric optics that achieve peak intensity at 60° and a sharp cut-off of light at 80°. The MHN-LA/FC lamps guarantee pleasant and natural color rendering and comfortable atmosphere.

Faydaları

- Breakthrough asymmetrical downlighting luminaire combines compact dimensions with high efficiency
- Available with narrow, medium and wide beams for flexibility in use; sharp beam cut-off for excellent control of spill light and limitation of glare and upward light leakage
- Can be used with metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation

Özellikler

- Kompakt boyutlar
- Yüksek verimlilik
- Metal halojenür ampuller veya yüksek basınçlı sodyum lambalarla kullanılabilir
- Dar, orta genişlikte ve geniş ışın seçenekleri
- Serpme ışık, parlama ve yukarı doğru sızma kontrolü

OptiVision MVP507

Uygulama

- Spor tesisleri
- Endüstriyel alanlar
- Araç park yerleri

Versions



OptiVision MVP507, světlo met pro sportoviště a plošné osvětlení

ÜRÜN BİLGİLERİ



aksesuarlar



Jednoduché zařízení pro směrování (ZVP507 SAD)

Ordercode 15427500

OptiVision MVP507

Onay ve Uygulama	
Mekanik çarpışma koruma kodu	IK08
Genel Bilgiler	
Top darbelerine dayanıklılık işareti	Ball Impact Resistance mark
CE işareti	CE mark
Işık kaynağı sayısı	1
Ürün Ailesi Kodu	MVP507
Mekanik Ayrıntılar ve Muhafaza	
Renk	Aluminum

Genel Bilgiler

Order Code	Full Product Name	Lamba		Lamba gücü	Optik sistem türü
		Işık kaynağı rengi	ailesi kodu		
15196000	MVP507 MHN-LA2000W/842 400V WB SI	842 nötr beyaz	MHN-LA	2000 W	Wide beam
15197700	MVP507 MHN-LA2000W/842 400V MB SI	842 nötr beyaz	MHN-LA	2000 W	Medium beam
15198400	MVP507 MHN-LA2000W/842 400V NB SI	842 nötr beyaz	MHN-LA	2000 W	Narrow beam
15201100	MVP507 HPI-T1000W WB	-	HPI-T	1000 W	Wide beam
15203500	MVP507 MHN-LA2000W 400V WB SI	-	MHN-LA	2000 W	Wide beam
15204200	MVP507 MHN-LA2000W 400V MB SI	-	MHN-LA	2000 W	Medium beam
15205900	MVP507 MHN-LA2000W 400V NB SI	-	MHN-LA	2000 W	Narrow beam
15207300	MVP507 MHN-LA2000W/956 400V WB SI	956 gün ışığı	MHN-LA	2000 W	Wide beam
15208000	MVP507 MHN-LA2000W/956 400V MB SI	956 gün ışığı	MHN-LA	2000 W	Medium beam
15209700	MVP507 MHN-LA2000W/956 400V NB SI	956 gün ışığı	MHN-LA	2000 W	Narrow beam
54628500	MVP507 SON-TP600W K WB SI	-	SON-TP	600 W	Wide beam
54629200	MVP507 SON-T1000W K WB SI	-	SON-T	1000 W	Wide beam
54630800	MVP507 MHN-LA1000W/842 230V WB SI	842 nötr beyaz	MHN-LA	1000 W	Wide beam
54631500	MVP507 SON-T600W WB SI	-	SON-T	600 W	Wide beam

Order Code	Full Product Name	Lamba		Lamba gücü	Optik sistem türü
		Işık kaynağı rengi	ailesi kodu		
54632200	MVP507 SON-T1000W WB SI	-	SON-T	1000 W	Wide beam
54633900	MVP507 MHN-LA1000W 230V WB SI	-	MHN-LA	1000 W	Wide beam
29134600	MVP507 MHN-FC2000W/740 400V NB SI	740 nötr beyaz	MHN-FC	2000 W	Narrow beam
29135300	MVP507 MHN-FC2000W/740 400V MB SI	740 nötr beyaz	MHN-FC	2000 W	Medium beam
29136000	MVP507 MHN-FC2000W/740 400V WB SI	740 nötr beyaz	MHN-FC	2000 W	Wide beam
29149000	MVP507 MHN-FC1000W/740 230V NB SI	740 nötr beyaz	MHN-FC	1000 W	Narrow beam
29150600	MVP507 MHN-FC1000W/740 230V MB SI	740 nötr beyaz	MHN-FC	1000 W	Medium beam
29251000	MVP507 MHN-FC1000W/740 230V WB SI	740 nötr beyaz	MHN-FC	1000 W	Wide beam
29577100	MVP507 MHN-LA2000W/842 400V WB SI SL	842 nötr beyaz	MHN-LA	2000 W	Wide beam
29578800	MVP507 MHN-LA2000W/842 400V MB SI SL	842 nötr beyaz	MHN-LA	2000 W	Medium beam
29579500	MVP507 MHN-LA2000W/842 400V NB SI SL	842 nötr beyaz	MHN-LA	2000 W	Narrow beam
29712600	MVP507 MHN-LA2000W/956 400V WB SI SL	956 gün ışığı	MHN-LA	2000 W	Wide beam

OptiVision MVP507

Order Code	Full Product Name	Lamba			
		Işık kaynağı rengi	ailesi kodu	Lamba gücü	Optik sistem türü
29713300	MVP507 MHN- LA2000W/956 400V MB SI SL	956 gün ışığı	MHN-LA	2000 W	Medium beam
29714000	MVP507 MHN- LA2000W/956 400V NB SI SL	956 gün ışığı	MHN-LA	2000 W	Narrow beam
29715700	MVP507 MHN- FC2000W/740 400V NB SI SL	740 nötr beyaz	MHN-FC	2000 W	Narrow beam

Order Code	Full Product Name	Lamba			
		Işık kaynağı rengi	ailesi kodu	Lamba gücü	Optik sistem türü
29716400	MVP507 MHN- FC2000W/740 400V MB SI SL	740 nötr beyaz	MHN-FC	2000 W	Medium beam
29717100	MVP507 MHN- FC2000W/740 400V WB SI SL	740 nötr beyaz	MHN-FC	2000 W	Wide beam
42131300	MVP507 MHN- LA1000W/956 WB SI	956 gün ışığı	MHN-LA	1000 W	Wide beam

