



Basic fluorescent lighting

TL-D Standard Colours

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Benefits

- Create atmospheres from warm white to cool daylight

Features

- Standard colors with moderate color rendering
- Available in various color designations

Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where color rendering is not an important factor

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


TL-D Standard Colours

Versions



LPPR TL-DSTD G13

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/54-765 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 36W/54-765 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

General Information	
Cap-Base	G13
Nominal lifetime	13,000 hour(s)
Light Technical	
Color Designation	Cool Daylight
Color rendering index (CRI)	72
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg

Light Technical

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
928048005436	TL-D 18W/54-765 1SL/25	6200 K	1,050 lm

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
928048505436	TL-D 36W/54-765 1SL/25	6500 K	2,500 lm

Operating and Electrical

TL-D Standard Colours

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048005436	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048505436	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
928048005436	TL-D 18W/54-765 1SL/25	22 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
928048505436	TL-D 36W/54-765 1SL/25	43 kWh

