



Circular shaped, basic fluorescent lighting

TL-E Circular Standard Colours

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.

Benefits

- Create atmospheres from warm white to cool daylight
- Symmetrical, omnidirectional light distribution

Features

- Standard colors with moderate color rendering and varying color designations

Application

- Suitable for use in a wide range of luminaires for various purposes, including many decorative luminaires where color rendering is not important

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


TL-E Circular Standard Colours

Versions



LPPR TL-ESTD G10q

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 22W/54-765 1CT/12	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm
TL-E 32W/33-640 1CT/12	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm
TL-E 32W/54-765 1CT/12	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

General Information	
Cap-Base	G10q
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	C-T29
Approval and Application	
Mercury (Hg) Content (Nom)	9 mg

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
928026205460	TL-E 22W/54-765 1CT/12	Cool Daylight	6200 K	72	48 lm/W	1,050 lm
928026303360	TL-E 32W/33-640 1CT/12	Cool White (CW)	4100 K	63	64 lm/W	2,050 lm
928026305460	TL-E 32W/54-765 1CT/12	Cool Daylight	6200 K	72	57 lm/W	1,750 lm

Operating and Electrical

TL-E Circular Standard Colours

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928026205460	TL-E 22W/54-765 1CT/12	0.400 A	62 V	22.0 W
928026303360	TL-E 32W/33-640 1CT/12	0.450 A	81 V	32.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928026305460	TL-E 32W/54-765 1CT/12	0.450 A	81 V	32.0 W

