



TMS122

Pentura TMS122 C

A high-quality dedicated batten luminaire for single and twin TL5 fluorescent lamps. The luminaire is integrated with a slim HF electronic ballast for compactness. This batten is suitable for both direct and indirect lighting applications.

Features

- The batten is built on a base plate, to be easily fixed to the ceiling
- Contains all the electrical and mechanical components, and a white pre-lacquered housing, fixed to the base-plate via 2 screws with no mechanical functionality
- The batten includes two plastic end caps and is integrated with HK electronic ballast

Application


- Shops
- Offices
- Industries
- Coves

Versions



Pentura TMS122 C

Dimensional drawing



Product	A	B
TMS122 1xTL5-14W EBC	485 mm	573 mm
TMS122 1xTL5-28W EBC	1085 mm	1173 mm
TMS122 2xTL5-14W EBC	485 mm	573 mm
TMS122 2xTL5-28W EBC	1085 mm	1173 mm
TMS122 1xTL5-28W HFS	1085 mm	1173 mm
TMS122 1xTL5-14W HFP	485 mm	573 mm
TMS122 1xTL5-28W HFP	1085 mm	1173 mm
TMS122 2xTL5-28W HFP	1085 mm	1173 mm
TMS122 2xTL5-14W HFS	485 mm	573 mm
TMS122 2xTL5-14W HFP	485 mm	573 mm
TMS122 1xTL5-14W HFS	485 mm	573 mm
TMS122 2xTL5-28W HFS	1085 mm	1173 mm

Approval and application

Ingress protection code IP20

General information

Protection class IEC Safety class I

Lamp family code TL5

General information

Order Code	Full Product Name	Gear	Lamp power	Number of light sources
910403358080	TMS122 1xTL5-14W EBC	EBE	14 W	1 pc
910403358180	TMS122 1xTL5-28W EBC	EBE	28 W	1 pc
910403358280	TMS122 2xTL5-14W EBC	EBE	14 W	2 pcs
910403358380	TMS122 2xTL5-28W EBC	EBE	28 W	2 pcs
911400863580	TMS122 1xTL5-28W HFS	EBS	28 W	1 pc
911400863680	TMS122 1xTL5-14W HFP	EBP	14 W	1 pc

Order Code	Full Product Name	Gear	Lamp power	Number of light sources
911400863780	TMS122 1xTL5-28W HFP	EBP	28 W	1 pc
911400863880	TMS122 2xTL5-28W HFP	EBP	28 W	2 pcs
911400865280	TMS122 2xTL5-14W HFS	EBS	14 W	2 pcs
911400865380	TMS122 2xTL5-14W HFP	EBP	14 W	2 pcs
911400865480	TMS122 1xTL5-14W HFS	EBS	14 W	1 pc
911400865580	TMS122 2xTL5-28W HFS	EBS	28 W	2 pcs

Mechanical and housing

Order Code	Full Product Name	Color
910403358080	TMS122 1xTL5-14W EBC	-
910403358180	TMS122 1xTL5-28W EBC	-
910403358280	TMS122 2xTL5-14W EBC	-
910403358380	TMS122 2xTL5-28W EBC	-
911400863580	TMS122 1xTL5-28W HFS	-
911400863680	TMS122 1xTL5-14W HFP	-

Order Code	Full Product Name	Color
911400863780	TMS122 1xTL5-28W HFP	-
911400863880	TMS122 2xTL5-28W HFP	-
911400865280	TMS122 2xTL5-14W HFS	-
911400865380	TMS122 2xTL5-14W HFP	-
911400865480	TMS122 1xTL5-14W HFS	-
911400865580	TMS122 2xTL5-28W HFS	-

