



MSR Gold™ MiniFastFit – lamp replacement in seconds

MSR Gold™ MiniFastFit (Touring/Stage)

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Benefits

- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High beam intensity

Features

- Philips MiniFastFit
- Compact design
- Innovative gold plated pins
- High color temperature
- Very short arc

MSR Gold™ MiniFastFit (Touring/Stage)

Application

- Events
- Shows
- Touring/Stage


Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



Dimensional drawing



Product

MSR Gold™ 700/2 MiniFastFit 1CT/4

MSR Gold™ 400 MiniFastFit 1CT/16

Controls and Dimming

Dimmable Yes

General Information

Cap-Base PGJX28

Life To 50% Failures (Nom) 750 h

Main Application Entertainment

Operating Position UNIVERSAL

System Description MiniFastFit

Operating and Electrical

MSR Gold™ MiniFastFit (Touring/Stage)


Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
15828800	MSR Gold™ 400 MiniFastFit 1CT/16	7.2 A	400 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
22117300	MSR Gold™ 700/2 MiniFastFit 1CT/4	10.2 A	700 W

Light Technical

Order Code	Full Product Name	Colour Code	Correlated Colour Temperature (Nom)	Colour Rendering Index (Nom)	Luminous Flux (Min)	Luminous Flux (Nom)
15828800	MSR Gold™ 400 MiniFastFit 1CT/16	-	6700 K	60	23400 lm	26000 lm
22117300	MSR Gold™ 700/2 MiniFastFit 1CT/4	2	7200 K	75	44000 lm	47000 lm

Colour Rendering Diagrams



XDCR_XDMSR_400W-Colour Rendering Vector diagram

