



MSR Gold™ MiniFastFit – lamp replacement in seconds

MSR Gold™ MiniFastFit (Touring/Stage)

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Benefits

- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High beam intensity

Features

- Philips MiniFastFit
- Compact design
- Innovative gold plated pins
- High color temperature
- Very short arc

MSR Gold™ MiniFastFit (Touring/Stage)

Application

- Events
- Shows
- Touring/Stage

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



MSR Gold™ 300/2 MiniFastFit




MSR Gold™ 400, 575/2, 700(1,2) MiniFastFit

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2 MiniFastFit 1CT/4	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm



Product
MSR Gold™ 700/2 MiniFastFit 1CT/4

MSR Gold™ MiniFastFit (Touring/Stage)

Controls and Dimming

Dimmable	Yes
----------	-----

General Information

Cap-Base	PGJX28
Life To 50% Failures (Nom)	750 h
Main Application	Entertainment
Operating Position	Universal
System Description	MiniFastFit

Light Technical

Color Code	2
------------	---

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
287177	MSR Gold™ 300/2 MiniFastFit 1CT/4	3.75 A	300 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
286922	MSR Gold™ 700/2 MiniFastFit 1CT/4	10.2 A	700 W

Light Technical

Order Code	Full Product Name	Correlated			
		Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Min)	Luminous Flux (Nom)
287177	MSR Gold™ 300/2 MiniFastFit 1CT/4	9300 K	80	19170 lm	21300 lm
286922	MSR Gold™ 700/2	7200 K	75	44000 lm	47000 lm

Order Code	Full Product Name	Correlated			
		Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Min)	Luminous Flux (Nom)
	MiniFastFit 1CT/4				

