



# PAR56 and PAR 64 – picking out the smallest of details

## PAR56 και PAR64

These self-contained spotlights are ideal for intensifying the visual experience in all kinds of clubs, that is because their accurate beam control picks out even the smallest of details even over long distances. This beam control makes the PAR 56 and PAR 64 excellent for long-range light projections. In addition, the universal burning feature provides complete flexibility of luminaire angle and position, while the front glass of the PAR56 provides thermal and physical protection. The result? Complete creative freedom to achieve the desired effect. Immediate re-strike also ensures instant resumption of entertainment after any power interruption.

### Οφέλη

- Allows details to be picked out over long distances with good beam control
- Excellent for long-range light projections
- Provides thermal and physical protection
- Allows fullest flexibility of luminaire angle and position to obtain the desired effect
- Immediate re-strike after any power interruption

### Χαρακτηριστικά

- Self-contained spotlight
- Front glass
- Universal burning
- Hot restrike

### Εφαρμογή


- Ideal for a wide range of performance and event lighting applications, for example in clubs, studios and theaters

# PAR56 και PAR64

## Versions



## Σχεδιάγραμμα διαστάσεων



Product	D (max)	C (max)
PAR64 1000W 230V NSP	204 mm	150 mm
PAR64 1000W 230V MFL	204 mm	150 mm

### Συστήματα ελέγχου και ρύθμιση της έντασης

Δυνατότητα ρύθμισης της έντασης φωτισμού	Ναι
--	-----

### Λειτουργία και ηλεκτρικά συστήματα

Τάση (ονομ.)	230 V
Ισχύς (ονομαστική) (ονομ.)	1000 W

### Γενικές πληροφορίες

Λυχνιολαβή	GX16D
Ονομαστική διάρκεια ζωής (ονομ.)	300 h
Διάρκεια ζωής έως 50% αστοχίας (ελάχ.)	300 h
Κύρια εφαρμογή	Flood and Ambient Lighting
Θέση λειτουργίας	UNIVERSAL

### Τεχνικός φωτισμός

Σχετική θερμοκρασία χρώματος (ονομ.)	3200 K
--------------------------------------	--------

### Μηχανικά εξαρτήματα και περίβλημα

Σχήμα λαμπτήρα	PAR64
----------------	-------

### Γενικές πληροφορίες

Order Code	Full Product Name	Κώδικας Ansi	Κωδικός LIF
44087710	PAR64 1000W 230V NSP	EXD	CP61
44089110	PAR64 1000W 230V MFL	EXE	CP62

## Τεχνικός φωτισμός

## PAR56 και PAR64

Order Code	Full Product Name	Γωνία δέσμης (ονομ.)	Περιγραφή δέσμης	Ένταση φωτός (μέγ.)
44087710	PAR64 1000W 230V NSP	12 °	Narrow Spot	290000 cd

Order Code	Full Product Name	Γωνία δέσμης (ονομ.)	Περιγραφή δέσμης	Ένταση φωτός (μέγ.)
44089110	PAR64 1000W 230V MFL	23 °	Medium Flood	130000 cd

