



CorePro LEDcapsule LV – For task lighting and decorative applications

CorePro LEDcapsule LV

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

Benefits

- Up to 88% energy saving compared with halogen lamps
- Up to 88% energy saving compared with halogen lamps
- Broad compatibility with transformers
- Broad compatibility with transformers
- Lower maintenance costs
- Lower maintenance costs

Features

- Easy retrofit
- Easy retrofit
- Lifetime of 15,000 hours
- Lifetime of 15,000 hours
- UV- and IR-free light
- UV- and IR-free light
- Free of mercury and hazardous materials
- Free of mercury and hazardous materials

CorePro LEDcapsule LV

Application

- Hotels, restaurants, bars, cafés
- Hotels, restaurants, bars, cafés
- Lobbies, corridors, stairwells, washrooms, reception areas, under-cabinet fixtures, cabinet lighting
- Lobbies, corridors, stairwells, washrooms, reception areas, under-cabinet fixtures, cabinet lighting

Versions





LED G4 12V Dim POS2



LED G4 12V 1 POS2

Dimensional drawing



Product	D	C
CorePro LEDcapsuleLV 1-10W G4 830	13 mm	35 mm

Product	D	C
CorePro LEDcapsuleLV 2.1-20W G4 827 D	15 mm	40 mm

CorePro LEDcapsule LV

General Information	
Cap-Base	G4
Switching Cycle	50,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Beam Angle (Nom)	300 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	- Hz
Line Frequency	- Hz
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	80 °C
Mechanical and Housing	
Bulb Shape	Capsule

Light Technical

		Correlated Color		
Order Code	Full Product Name	Temperature (Nom)	Color Code	Luminous Flux
929002389402	CorePro LEDcapsuleLV 2.1-20W G4	2700 K	827	210 lm
	827 D			
929002388902	CorePro LEDcapsuleLV 1-10W G4 830	3000 K	830	120 lm

Operating and Electrical

		Power	Wattage
Order Code	Full Product Name	Consumption	Equivalent
929002389402	CorePro LEDcapsuleLV 2.1-20W G4 827 D	2.1 W	20 W

		Power	Wattage
Order Code	Full Product Name	Consumption	Equivalent
929002388902	CorePro LEDcapsuleLV 1-10W G4 830	1 W	10 W


Controls and Dimming

Order Code	Full Product Name	Dimmable
929002389402	CorePro LEDcapsuleLV 2.1-20W G4 827 D	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929002388902	CorePro LEDcapsuleLV 1-10W G4 830	No

Approval and Application

		Energy Consumption kWh/
Order Code	Full Product Name	1000 h
929002389402	CorePro LEDcapsuleLV 2.1-20W G4 827 D	3 kWh
929002388902	CorePro LEDcapsuleLV 1-10W G4 830	1 kWh



CorePro LEDcapsule LV

