



Energy saving upgrade without sacrifice

Halogen A19

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar A-shape design. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Benefits

- A bright, energy saving alternative to standard incandescents.
- Halogen Soft White is ideal for warm colors and natural wood finishes.
- Halogen Natural Light provides light similar to natural daylight and brings out the true vibrant colors in your home.
- Halogen Twice the Life provides 2000 hours of rated average life.

Features


- Provides 28% more energy savings
- Fully dimmable and Instant-on
- Mercury Free
- Rated average life of 1000-2000 hours
- Halogen complies with the EISA 2007 efficiency standards for 2012-2014

Application

- Ideal for indoor table, floor lamps and other household fixtures.

Halogen A19

Dimensional drawing



Product	D	C (max)
29A19/EV/CL 120V 12/2	2.375 inch	4.13 inch
EcoV MS 53W E26 120V A19(A60) SWR 6/4	2.36 inch	4.17 inch

General Information	
Cap-Base	E26
Rated Lifetime (Hours)	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Material	Glass
Bulb Shape	A19

General Information

Order Code	Full Product Name	Nominal lifetime
925702136301	29A19/EV/CL 120V 12/2	1,000 hour(s)

Order Code	Full Product Name	Nominal lifetime
925716436302	EcoV MS 53W E26 120V A19(A60) SWR 6/4	-

Light Technical

Order Code	Full Product Name	Luminous Flux
925702136301	29A19/EV/CL 120V 12/2	-

Order Code	Full Product Name	Luminous Flux
925716436302	EcoV MS 53W E26 120V A19(A60) SWR 6/4	850 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
925702136301	29A19/EV/CL 120V 12/2	29 W

Order Code	Full Product Name	Power Consumption
925716436302	EcoV MS 53W E26 120V A19(A60) SWR 6/4	53 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
925702136301	29A19/EV/CL 120V 12/2	Clear

Order Code	Full Product Name	Bulb Finish
925716436302	EcoV MS 53W E26 120V A19(A60) SWR 6/4	Soft White Red

Halogen A19

