



# Product Description

## Plusline Compact

Mains-voltage linear lamp giving white halogen light

### Benefits

- Bright halogen light
- Long lifetime


### Features

- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Constant light output during life

### Application

- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites

### Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline C 100W R7s 230V 1CT/10X10F	12 mm	76.5 mm	74.9 mm	73.3 mm	78 mm
Plusline C 100W R7s 240V 1BC/10	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm
Plusline C 150W R7s 230V 1CT/10X10F	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm
Plusline C 150W R7s 240V 1BC/12	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

# Plusline Compact

## General Information

Rated Lifetime (Hours)	2.000 hour(s)
Nominal lifetime	2.000 hour(s)
Operating Position	UNIVERSAL

## Light Technical

Color rendering index (CRI)	100
-----------------------------	-----

## Operating and Electrical

Starting Time (Nom)	0.0 s
---------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T3

## General Information

Order Code	Full Product Name	Cap-Base
923919943202	Plusline C 150W R7s 230V 1CT/10X10F	R7s
923919945709	Plusline C 150W R7s 240V 1BC/12	R7S
923920043290	Plusline C 100W R7s 230V 1CT/10X10F	R7s
923920045792	Plusline C 100W R7s 240V 1BC/10	R7S

## Light Technical

Order Code	Full Product Name	Correlated		
		Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923919943202	Plusline C 150W R7s 230V 1CT/10X10F	-	16 lm/W	2,400 lm
923919945709	Plusline C 150W R7s 240V 1BC/12	-	16 lm/W	2,400 lm

Order Code	Full Product Name	Correlated		
		Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923920043290	Plusline C 100W R7s 230V 1CT/10X10F	2800 K	15.5 lm/W	1,550 lm
923920045792	Plusline C 100W R7s 240V 1BC/10	-	15.5 lm/W	1,550 lm

## Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
923919943202	Plusline C 150W R7s 230V 1CT/10X10F	0.65 A	230 V	150 W
923919945709	Plusline C 150W R7s 240V 1BC/12	0.63 A	240 V	150 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
923920043290	Plusline C 100W R7s 230V 1CT/10X10F	0.43 A	230 V	100 W
923920045792	Plusline C 100W R7s 240V 1BC/10	0.42 A	240 V	100 W

