



Product Description

Plusline Small

Mains-voltage linear lamp giving white halogen light

Benefits

- · Bright halogen light
- · Long lifetime


Features

- · Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- · Two arc-preventing fuses for greater safety
- · Excellent colour rendering
- · Constant light output during life

Application

- Typically used in shop lighting applications
- · Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites

Dimensional drawing



| Product | D (max) | B (max) | В | B (min) | C (max) |
|-------------------------------|---------|----------|----------|----------|----------|
| Plusline S 300W R7s 230V 1CT/ | 12 mm | 115.8 mm | 114.2 mm | 112.6 mm | 117.6 mm |
| 10X10F | | | | | |
| Plusline S 500W R7s 230V 1CT/ | 12 mm | 115.8 mm | 114.2 mm | 112.6 mm | 117.6 mm |
| 10X10F | | | | | |

Plusline Small

| General Information | |
|------------------------------------|---------------|
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Nominal lifetime | 2,000 hour(s) |
| Operating Position | UNIVERSAL |
| | |
| Light Technical | |
| Correlated Color Temperature (Nom) | 2900 K |
| Color rendering index (CRI) | 100 |
| | |
| Operating and Electrical | |
| Voltage (Nom) | 230 V |
| Starting Time (Nom) | 0.0 s |
| | |
| Controls and Dimming | |
| Dimmable | Yes |
| | |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | T3 |

General Information

| Order Code | Full Product Name | Cap-Base |
|------------|-------------------------------------|----------|
| 80895700 | Plusline S 300W R7s 230V 1CT/10X10F | R7s |
| 80901500 | Plusline S 500W R7s 230V 1CT/10X10F | R7S |

Light Technical

| | | Luminous Efficacy | |
|------------|-------------------------------|-------------------|---------------|
| Order Code | Full Product Name | (rated) (Nom) | Luminous Flux |
| 80895700 | Plusline S 300W R7s 230V 1CT/ | 17 lm/W | 5,114 lm |
| | 10X10F | | |

| | | Luminous Efficacy | |
|------------|-------------------------------|-------------------|---------------|
| Order Code | Full Product Name | (rated) (Nom) | Luminous Flux |
| 80901500 | Plusline S 500W R7s 230V 1CT/ | 19.3 lm/W | 9,660 lm |
| | 10X10F | | |

Operating and Electrical

| | | Lamp Current | |
|------------|-------------------------------|--------------|-------------------|
| Order Code | Full Product Name | (Nom) | Power Consumption |
| 80895700 | Plusline S 300W R7s 230V 1CT/ | 1.3 A | 300 W |
| | 10X10F | | |

| | | Lamp Current | |
|------------|-------------------------------|--------------|-------------------|
| Order Code | Full Product Name | (Nom) | Power Consumption |
| 80901500 | Plusline S 500W R7s 230V 1CT/ | 2.17 A | 500 W |
| | 10X10F | | |



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.