



Product Description

Plusline Small

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Long lifetime

Features

- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Constant light output during life

Application

- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites


Plusline Small

Versions




LPPR HLINEAR 0001

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
PLUS PRO S 500W R7s 230V 1CT/50	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
PLUS PRO S 500W R7s 230V T3 CL 1BC	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 200W R7s 230V 1CT/10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 200W R7s 240V 1BC/10	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 300W R7s 230V 1CT/10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 300W R7s 230V 1CT/10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 300W R7s 240V 1BC/10	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 500W R7s 230V 1CT/10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 500W R7s 230V 1CT/10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 500W R7s 240V 1BC/12	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

Product	D (max)	C (max)
PLUS PRO S 1000W 240-250V CL 1SL	12.75 mm	114.2 mm



Plusline Small

General Information

Rated Lifetime (Hours)	2,000 hour(s)
Operating Position	UNIVERSAL

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
924735444201	Plusline S 300W R7s 230V 1CT/10X10F	R7s	2,000 hour(s)
924735444289	Plusline S 300W R7s 230V 1CT/10X10F	R7S	2,000 hour(s)
924735445597	Plusline S 300W R7s 240V 1BC/10	R7S	2,000 hour(s)
924735544201	Plusline S 500W R7s 230V 1CT/10X10F	R7S	2,000 hour(s)
924735544280	PLUS PRO S 500W R7s 230V T3 CL 1BC	R7s	2,000 hour(s)
924735544298	Plusline S 500W R7s 230V 1CT/10X10F	R7s	2,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
924735545501	Plusline S 500W R7s 240V 1BC/12	R7S	2,000 hour(s)
924735744201	Plusline S 200W R7s 230V 1CT/10X10F	R7S	2,000 hour(s)
924735745597	Plusline S 200W R7s 240V 1BC/10	R7S	2,000 hour(s)
925632544211	PLUS PRO S 500W R7s 230V 1CT/50	R7s	2,000 hour(s)
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	R7S	-

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
		(Nom)	(CRI)	(Nom)	(Nom)
924735444201	Plusline S 300W R7s 230V 1CT/10X10F	2900 K	100	17 lm/W	5,114 lm
924735444289	Plusline S 300W R7s 230V 1CT/10X10F	2900 K	100	17 lm/W	5,114 lm
924735445597	Plusline S 300W R7s 240V 1BC/10	-	100	17 lm/W	5,114 lm
924735544201	Plusline S 500W R7s 230V 1CT/10X10F	2900 K	100	19.3 lm/W	9,660 lm
924735544280	PLUS PRO S 500W R7s 230V T3 CL 1BC	2900 K	100	19.3 lm/W	9,660 lm
924735544298	Plusline S 500W R7s	2900 K	100	19.3 lm/W	9,660 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
		(Nom)	(CRI)	(Nom)	(Nom)
924735444201	Plusline S 300W R7s 230V 1CT/10X10F	2900 K	100	17 lm/W	5,114 lm
924735545501	Plusline S 500W R7s 240V 1BC/12	2900 K	100	19.3 lm/W	9,660 lm
924735744201	Plusline S 200W R7s 230V 1CT/10X10F	2900 K	100	15 lm/W	3,000 lm
924735745597	Plusline S 200W R7s 240V 1BC/10	2900 K	100	15 lm/W	3,000 lm
925632544211	PLUS PRO S 500W R7s 230V 1CT/50	2900 K	100	19.8 lm/W	9,900 lm
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	-	-	-	22,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp			Starting Time (Nom)
		Current (Nom)	Voltage (Nom)	Power Consumption	(Nom)
924735444201	Plusline S 300W R7s 230V 1CT/10X10F	1.3 A	230 V	300 W	0.0 s

Order Code	Full Product Name	Lamp			Starting Time (Nom)
		Current (Nom)	Voltage (Nom)	Power Consumption	(Nom)
924735444289	Plusline S 300W R7s 230V 1CT/10X10F	1.3 A	230 V	300 W	0.0 s
924735445597	Plusline S 300W R7s 240V 1BC/10	1.25 A	240 V	300 W	0.0 s

Plusline Small

Order Code	Full Product Name	Lamp			Starting Time (Nom)
		Current (Nom)	Voltage (Nom)	Power Consumption	
924735544201	Plusline S 500W R7s 230V 1CT/10X10F	2.17 A	230 V	500 W	0.0 s
924735544280	PLUS PRO S 500W R7s 230V T3 CL 1BC	2.17 A	230 V	500 W	0.0 s
924735544298	Plusline S 500W R7s 230V 1CT/10X10F	2.17 A	230 V	500 W	0.0 s
924735545501	Plusline S 500W R7s 240V 1BC/12	2.08 A	240 V	500 W	0.0 s

Order Code	Full Product Name	Lamp			Starting Time (Nom)
		Current (Nom)	Voltage (Nom)	Power Consumption	
924735744201	Plusline S 200W R7s 230V 1CT/10X10F	0.87 A	230 V	200 W	0.0 s
924735745597	Plusline S 200W R7s 240V 1BC/10	0.83 A	240 V	200 W	0.0 s
925632544211	PLUS PRO S 500W R7s 230V 1CT/50	2.17 A	230 V	500.0 W	0.0 s
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	-	240-250 V	1,000 W	-

Controls and Dimming

Order Code	Full Product Name	Dimmable
924735444201	Plusline S 300W R7s 230V 1CT/10X10F	Yes
924735444289	Plusline S 300W R7s 230V 1CT/10X10F	Yes
924735445597	Plusline S 300W R7s 240V 1BC/10	Yes
924735544201	Plusline S 500W R7s 230V 1CT/10X10F	Yes
924735544280	PLUS PRO S 500W R7s 230V T3 CL 1BC	Yes
924735544298	Plusline S 500W R7s 230V 1CT/10X10F	Yes

Order Code	Full Product Name	Dimmable
924735545501	Plusline S 500W R7s 240V 1BC/12	Yes
924735744201	Plusline S 200W R7s 230V 1CT/10X10F	Yes
924735745597	Plusline S 200W R7s 240V 1BC/10	Yes
925632544211	PLUS PRO S 500W R7s 230V 1CT/50	Yes
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
924735444201	Plusline S 300W R7s 230V 1CT/10X10F	T3
924735444289	Plusline S 300W R7s 230V 1CT/10X10F	T3
924735445597	Plusline S 300W R7s 240V 1BC/10	T3
924735544201	Plusline S 500W R7s 230V 1CT/10X10F	T3
924735544280	PLUS PRO S 500W R7s 230V T3 CL 1BC	T3
924735544298	Plusline S 500W R7s 230V 1CT/10X10F	T3

Order Code	Full Product Name	Bulb Shape
924735545501	Plusline S 500W R7s 240V 1BC/12	T3
924735744201	Plusline S 200W R7s 230V 1CT/10X10F	T3
924735745597	Plusline S 200W R7s 240V 1BC/10	T3
925632544211	PLUS PRO S 500W R7s 230V 1CT/50	T11
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	T37

