



Product Description

CLASSICTONE Superlux

Mushroom-shaped (E-shaped) lamps in various diameters

Benefits

- Gives up to 35% more light on the working plane with no extra energy consumption

Features

- Partial white bulb finish with a white window in a mushroom shape
- Shields the filament and directs light to where it is needed
- Universal burning Position

Application


- Wherever higher local lighting levels are required, e.g. for reading or task lighting

Versions



CLASSICTONE Superlux

Dimensional drawing



Product	D	C (max)
CLASSICTONE 60W E27 220-240V E50 W-W 1CT/10X10F	50 mm	91 mm
CLASSICTONE 40W E27 220-240V E50 W-W 1CT/10X10F	50 mm	91 mm
CLASSICTONE 100W E27 220-240V E60 W-W 1CT	60 mm	104 mm
CLASSICTONE 25W E27 220-240V E50 W-W 1CT/10X10F	50 mm	91 mm

Approval and Application	
Energy Efficiency Label (EEL)	E
Controls and Dimming	
Dimmable	yes
Operating and Electrical	
Voltage (Nom)	220-240 V
General Information	
Cap-Base	E27
Nominal Lifetime (Nom)	1000 h
Operating Position	UNIVERSAL
Light Technical	
Colour Rendering Index (Nom)	100
Mechanical and Housing	
Bulb Finish	White-Window

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
920220843329	CLASSICTONE 25W E27 220-240V E50 W-W 1CT/10X10F	25 W
920226243329	CLASSICTONE 40W E27 220-240V E50 W-W 1CT/10X10F	40 W
920236243329	CLASSICTONE 60W E27 220-240V E50 W-W 1CT/10X10F	60 W
920246243329	CLASSICTONE 100W E27 220-240V E60 W-W 1CT	100 W

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
920220843329	CLASSICTONE 25W E27 220-240V E50 W-W 1CT/10X10F	210 lm
920226243329	CLASSICTONE 40W E27 220-240V E50 W-W 1CT/10X10F	400 lm

Order Code	Full Product Name	Luminous Flux (Nom)
920236243329	CLASSICTONE 60W E27 220-240V E50 W-W 1CT/10X10F	680 lm
920246243329	CLASSICTONE 100W E27 220-240V E60 W-W 1CT	1280 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
920220843329	CLASSICTONE 25W E27 220-240V E50 W-W 1CT/10X10F	E50
920226243329	CLASSICTONE 40W E27 220-240V E50 W-W 1CT/10X10F	E50

Order Code	Full Product Name	Bulb Shape
920236243329	CLASSICTONE 60W E27 220-240V E50 W-W 1CT/10X10F	E50
920246243329	CLASSICTONE 100W E27 220-240V E60 W-W 1CT	E60

