

Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features


- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI > 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LEDbulbs


Versions



Dimensional drawing

D

Product	D	C
LEDClas 7.5-60W A60 E27 2000K GOLD APR	60 mm	112 mm



Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm

Classic filament LEDbulbs

Approval and Application

Energy Efficiency Label (EEL) A+

Controls and Dimming

Dimmable Yes

Operating and Electrical

Input Frequency 50 to 60 Hz

Voltage (Nom) 220-240 V

Wattage Equivalent 60 W

Starting Time (Nom) 0.5 s

General Information

Cap-Base E27

Nominal Lifetime (Nom) 15000 h

Switching Cycle 20000X

Light Technical

Colour Code 820

Correlated Colour Temperature (Nom) 2000 K

Colour Rendering Index (Nom) 80

Llmf At End Of Nominal Lifetime (Nom) 70 %

Mechanical and Housing

Bulb Finish Gold Clear

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	8 kWh
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	7 kWh

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	7.5 W

Order Code	Full Product Name	Power (Rated) (Nom)
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	7 W



Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	600 lm

Order Code	Full Product Name	Luminous Flux (Nom)
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	630 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	A60
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	G120



Classic filament LEDbulbs

