



# Classic LEDbulbs lamps for decorative lighting

## Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

### Features



- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI > 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

### Application



- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

# Classic filament LEDbulbs

## Versions



## Dimensional drawing







Product	D	C
LEDClassic 4-50W ST64 E27 WW CL ND APR	64 mm	140 mm

Product	D	C
LEDClassic 2-25W B35 E14 WW CL ND APR	35 mm	97 mm

# Classic filament LEDbulbs

## Dimensional drawing



Product	D	C
LEDClassic 2-25W P45 E27 WW CL ND APR	45 mm	78 mm

Product	D	C
LEDClassic 2-25W P45 E14 WW CL ND APR	45 mm	80 mm

Product	D	C
LEDClassic 4-50W A60 E27 WW CL ND APR	60 mm	104 mm

Product	D	C
LEDClassic 2-25W BA35 E14 WW CL ND APR	35 mm	123 mm

# Classic filament LEDbulbs

## Approval and Application

Energy Efficiency Label (EEL) A++

## Controls and Dimming

Dimmable No

## Operating and Electrical

Input Frequency 50 to 60 Hz

Voltage (Nom) 220-240 V

Starting Time (Nom) 0.5 s

## General Information

Nominal Lifetime (Nom) 15000 h

Rated Lifetime (Hours) 15000 h

Switching Cycle 20000X

## Light Technical

Colour Code 827

Correlated Colour Temperature (Nom) 2700 K

Colour Rendering Index (Nom) 80

Llmf At End Of Nominal Lifetime (Nom) 70 %

## Mechanical and Housing

Bulb Finish Clear

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	4 kWh
929001237308	LEDClassic 4-50W ST64 E27 WW CL ND APR	4 kWh
929001238308	LEDClassic 2-25W B35 E14 WW CL ND APR	2 kWh
929001238408	LEDClassic 2-25W BA35 E14 WW CL ND APR	2 kWh
929001238608	LEDClassic 2-25W P45 E14 WW CL ND APR	2 kWh
929001238708	LEDClassic 2-25W P45 E27 WW CL ND APR	2 kWh

## Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	50 W	4 W
929001237308	LEDClassic 4-50W ST64 E27 WW CL ND APR	50 W	4 W
929001238308	LEDClassic 2-25W B35 E14 WW CL ND APR	25 W	2 W

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001238408	LEDClassic 2-25W BA35 E14 WW CL ND APR	25 W	2 W
929001238608	LEDClassic 2-25W P45 E14 WW CL ND APR	25 W	2 W
929001238708	LEDClassic 2-25W P45 E27 WW CL ND APR	25 W	2 W

## General Information

Order Code	Full Product Name	Cap-Base
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	E27
929001237308	LEDClassic 4-50W ST64 E27 WW CL ND APR	E27
929001238308	LEDClassic 2-25W B35 E14 WW CL ND APR	E14

Order Code	Full Product Name	Cap-Base
929001238408	LEDClassic 2-25W BA35 E14 WW CL ND APR	E14
929001238608	LEDClassic 2-25W P45 E14 WW CL ND APR	E14
929001238708	LEDClassic 2-25W P45 E27 WW CL ND APR	E27

## Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	470 lm	470 lm
929001237308	LEDClassic 4-50W ST64 E27 WW CL ND APR	470 lm	470 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001238308	LEDClassic 2-25W B35 E14 WW CL ND APR	250 lm	250 lm
929001238408	LEDClassic 2-25W BA35 E14 WW CL ND APR	250 lm	250 lm

## Classic filament LEDbulbs

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001238608	LEDClassic 2-25W P45 E14 WW CL ND APR	250 lm	250 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001238708	LEDClassic 2-25W P45 E27 WW CL ND APR	250 lm	250 lm

### Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	A60
929001237308	LEDClassic 4-50W ST64 E27 WW CL ND APR	ST64
929001238308	LEDClassic 2-25W B35 E14 WW CL ND APR	B35
929001238408	LEDClassic 2-25W BA35 E14 WW CL ND APR	BA35
929001238608	LEDClassic 2-25W P45 E14 WW CL ND APR	P45
929001238708	LEDClassic 2-25W P45 E27 WW CL ND APR	P45

