



ClassicStreet – Echoing the past, shaped for the future

ClassicStreet brackets

Recalling the iconic beauty of 20th-century street lanterns, ClassicStreet combines elegant design with the subtle details of heritage luminaires while meeting today's urban lighting requirements. Though echoing the past, the ClassicStreet luminaire is very much shaped for the future. Its gently curved design, together with dedicated brackets and poles, creates a contemporary look that beautifies our cities and creates distinctive and warm night- and daytime ambiances. Not only in historical and traditional architectural settings, but also in more modern urban environments too. Designed around its LED engine, ClassicStreet delivers outstanding levels of lighting and energy performance.

Benefits

- Distinctive contemporary design inspired by classical complete street-lighting sets
- Fits both traditional and historical architectural settings as well as more modern environments
- Dedicated interfaces with ClassicStreet luminaire for optimum design integration and installation

Features

- Available in post-top and suspended versions
- Dedicated ClassicStreet brackets and poles
- Compatible with all Philips standard and advanced public lighting systems
- Optimised optics to deliver efficient and comfortable lighting levels

ClassicStreet brackets

Application


- City centres
- Roads and streets
- Residential areas
- Parks and plazas

Specifications


Type	JGB794 (ClassicStreet bracket suspended)
	JGB795 (ClassicStreet bracket post top)
Material	Steel
Colour	Dark grey (DGR), black (BK)
	Other RAL and AKZO Futura colours available on request

Installation	Tenon versions for mounting on Ø 60 mm poles with inserts
	Cap versions for mounting on Ø 76 mm poles
	Recommended mounting height: 4-6 m

Versions





ClassicStreet JGB794 dedicated post-top bracket for Ø 60 mm pole, single arm version



ClassicStreet brackets

Versions



Product details




ClassicStreet_brackets-JGB794-DP06



Tenon and cap versions



Suspended and post top versions



ClassicStreet_brackets-JGB795-DP05

General Information

ClassicStreet brackets

Order Code	Full Product Name	Product Family Code
21645100	JGB794 MBP-S 750 60 BK	JGB794
21646800	JGB794 MBP-T 750 60 BK	JGB794
21647500	JGB794 MBW 750 BK	JGB794
21648200	JGB795 MBP-S 750 60 BK	JGB795
21649900	JGB795 MBP-T 750 60 BK	JGB795

Order Code	Full Product Name	Product Family Code
21650500	JGB795 MBW 750 BK	JGB795
21651200	JGB794 MBP-S 750 76 BK	JGB794
21652900	JGB794 MBP-T 750 76 BK	JGB794
21653600	JGB795 MBP-S 750 76 BK	JGB795
21654300	JGB795 MBP-T 750 76 BK	JGB795

