# **PHILIPS** Lighting



# Simple and flexible solution to design modern light lines in professional and retail spaces

### PlainView, suspended

Light line solutions are always in fashion. therefore we know that delivering innovation in this field is crucial. PlainView is a modern looking, neat luminaire offering comfortable, good quality lighting and can also work as a design element. The luminaires offer high quality specifications and flexibility with different options for lumen packages. Thanks to these features and benefits, PlainView delivers ideal lighting in the non-working areas of professional spaces such as offices, educational institutes, and also the welcoming areas and entrances of retail spaces.

#### Benefits

- Clean and uniform light
- Multiple application use
- Easy to install and maintain
- Long lasting, reliable luminaire

#### Features

- Homogeneous exit window
- Can create standalone and continuous lines of light and offers recessed and suspended variants
- Same modules are used for standalone and continuous light lines providing flexibility and making installation easier
- Delivers Philips quality

#### Application

- Office circulation and common areas
- Education circulation and common areas
- $\cdot$  Retail general lighting in stores
- $\cdot$  Healthcare circulation and common areas

#### **Specifications**

Ambient Temperature	+10 to +40 °C	Initial luminous flux	3800 lm
Beam spread luminaire	100°	Input frequency	50 to 60 Hz
Main color of the	White	Input voltage	220 to 240 V
Luminaire		Inrush current (A)	22 A
Connection	Push-in connector 5-pole (PI) (Push-in connector 5-pole (PI))	Light source color	840 neutral white
Dimming	Yes	Light source	No
Driver	Power supply unit with DALI interface (PSD)	replaceable	
Initial correlated color	4000 K	Material	Housing: aluminum
temperature		Material	Reflector: -
Initial input power	40 W	Optic	No   -
Initial LED luminaire	90 lm/W	Optical cover	-
efficacy		Warranty period	5 years

#### Versions



#### **Product details**



PlainView\_Suspended-SP140P-1DPP.tif PlainView\_Suspended-SP140P-2DPP.tif

## PlainView, suspended

#### **Product details**



PlainView\_Suspended-SP140P-3DPP.tif



PlainView\_Suspended-SP140P-4DPP.tif



PlainView\_Suspended-SP140P-5DPP.tif



PlainView\_Suspended-SP140P-7DPP.tif



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2021, November 22 - data subject to change