

# Designed to be seen, looks good on or off

## Decorative LED bulbs

The new Deco collection (bulb) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

### Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

### Features

- Perfect fit and high-quality finishing
- High colour-rendering (CRI > 80) for vivid colours
- Eco-friendly: contains no mercury or other hazardous substances

### Application


- Perfect for decorative installations: domestic applications, hospitality (restaurants and hotels)

# Decorative LED bulbs

## Versions



## Dimensional drawing



Product	D	C
LED Classic CM A60 30W WW E27 CL ND SRT4	60 mm	104 mm
LED classic CM 48W A60 E27 WW CL D SRT4	60 mm	104 mm

### Operating and Electrical

Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s

### General Information

Cap-Base	E27
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20,000X

### Light Technical

Colour Code	827
Correlated Colour Temperature (Nom)	2700 K
Colour Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %

### Mechanical and Housing

Bulb Shape	A60
------------	-----

### Temperature

T-Case Maximum (Nom)	55 °C
----------------------	-------

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001276458	LED Classic CM A60 30W WW E27 CL ND SRT4	4 kWh	A++
929001333501	LED classic CM 48W A60 E27 WW CL D SRT4	8 kWh	A+

## Controls and Dimming

## Decorative LED bulbs

Order Code	Full Product Name	Dimmable
929001276458	LED Classic CM A60 30W WW E27 CL ND SRT4	No

Order Code	Full Product Name	Dimmable
929001333501	LED classic CM 48W A60 E27 WW CL D SRT4	Yes

### Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001276458	LED Classic CM A60 30W WW E27 CL ND SRT4	30 W	3.5 W

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001333501	LED classic CM 48W A60 E27 WW CL D SRT4	48 W	7.5 W

### Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
929001276458	LED Classic CM A60 30W WW E27 CL ND SRT4	370 lm
929001333501	LED classic CM 48W A60 E27 WW CL D SRT4	610 lm

