



**SmartBright
Suspension is the
most economic LED
linear solution.
Quality light with
good uniformity &
visual comfort is
delivered under
suspension
installation.**

SmartBright Suspension

Linear suspension solution with affordable price

Benefits

- Stylish product look & feel
- Excellent uniformity for light exit window
- Visual Comfort with enough light output

SmartBright Suspension

Features

- System efficacy up to 90lm/W
- Lumen output up to 3000lm/1.2m
- Flicker Free for good on site experience

Application

- Office
- Retail
- Open Area

Versions



RC095V W12L120



RC095V W12L120



RC095V W07L120



RC095V W07L120

Accessories



Ordercode 911401724662,
911401724682, 911401724722

Application Conditions

| | |
|-------------------------------|---------------|
| Ambient temperature range | -10 to +35 °C |
| Suitable for random switching | No |

Approval and Application

| | |
|------------------------------|------|
| Mech. impact protection code | IK03 |
| Ingress protection code | IP20 |

Controls and Dimming

| | |
|----------|----|
| Dimmable | No |
|----------|----|

General Information

| | |
|--------------------------|--------------------------------------|
| CE mark | - |
| Protection class IEC | Safety class I |
| Optical cover/lens type | Polystyrene bowl/ cover prismatic |
| Driver included | Yes |
| ENEC mark | - |
| Flammability mark | - |
| Glow-wire test | Temperature 650 °C, duration 30 s |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Optic type | Symmetrical |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Init. Color Rendering Index | >80 |
| Luminous flux tolerance | +/-10% |

Application Conditions

| Order Code | Full Product Name | Maximum dim level |
|--------------|--|-------------------|
| 911401723452 | RC095V LED30S/840 PSU W12L120 Black | Not applicable |
| 911401723472 | RC095V LED30S/865 PSU W12L120 Black | Not applicable |
| 911401723512 | RC095V LED15S/865 PSU W12L60 Black | Not applicable |
| 911401723462 | RC095V LED30S/840 PSU W12L120 Grey | Not applicable |
| 911401723482 | RC095V LED30S/865 PSU W12L120 Grey | Not applicable |
| 911401723492 | RC095V LED15S/840 PSU W12L60 Black | Not applicable |
| 911401723502 | RC095V LED15S/840 PSU W12L60 Grey | Not applicable |
| 911401723522 | RC095V LED15S/865 PSU W12L60 Grey | Not applicable |
| 911401723692 | RC095V LED30S/830 PSU W12L120 Grey GM | Not applicable |
| 911401723702 | RC095V LED30S/840 PSU W12L120 Grey GM | Not applicable |
| 911401723712 | RC095V LED30S/865 PSU W12L120 Grey GM | Not applicable |
| 911401723722 | RC095V LED15S/830 PSU W12L60 Grey GM | Not applicable |
| 911401723732 | RC095V LED15S/840 PSU W12L60 Grey GM | Not applicable |
| 911401723742 | RC095V LED15S/865 PSU W12L60 Grey GM | Not applicable |
| 911401723752 | RC095V LED30S/840 PSU W12L120 Grey RCA | 0% (digital) |
| 911401723762 | RC095V LED30S/865 PSU W12L120 Grey RCA | 0% (digital) |
| 911401723532 | RC095V LED26S/840 PSU W07L120 Black | Not applicable |
| 911401723552 | RC095V LED26S/865 PSU W07L120 Black | Not applicable |
| 911401723572 | RC095V LED13S/840 PSU W07L60 Black | Not applicable |
| 911401723592 | RC095V LED13S/865 PSU W07L60 Black | Not applicable |
| 911401723542 | RC095V LED26S/840 PSU W07L120 Grey | Not applicable |
| 911401723562 | RC095V LED26S/865 PSU W07L120 Grey | Not applicable |
| 911401723582 | RC095V LED13S/840 PSU W07L60 Grey | Not applicable |
| 911401723602 | RC095V LED13S/865 PSU W07L60 Grey | Not applicable |
| 911401723632 | RC095V LED26S/830 PSU W07L120 Black TW | Not applicable |
| 911401723642 | RC095V LED26S/830 PSU W07L120 Grey TW | Not applicable |
| 911401723652 | RC095V LED26S/840 PSU W07L120 Black TW | Not applicable |
| 911401723662 | RC095V LED26S/840 PSU W07L120 Grey TW | Not applicable |
| 911401723672 | RC095V LED26S/865 PSU W07L120 Black TW | Not applicable |
| 911401723682 | RC095V LED26S/865 PSU W07L120 Grey TW | Not applicable |

Operating and Electrical

| Order Code | Full Product Name | Input Voltage | Order Code | Full Product Name | Input Voltage |
|--------------|--|---------------|--------------|--|---------------|
| 911401723452 | RC095V LED30S/840 PSU W12L120 Black | 220 to 240 V | 911401723762 | RC095V LED30S/865 PSU W12L120 Grey RCA | 220-240 V |
| 911401723472 | RC095V LED30S/865 PSU W12L120 Black | 220 to 240 V | 911401723532 | RC095V LED26S/840 PSU W07L120 Black | 220 to 240 V |
| 911401723512 | RC095V LED15S/865 PSU W12L60 Black | 220 to 240 V | 911401723552 | RC095V LED26S/865 PSU W07L120 Black | 220 to 240 V |
| 911401723462 | RC095V LED30S/840 PSU W12L120 Grey | 220 to 240 V | 911401723572 | RC095V LED13S/840 PSU W07L60 Black | 220 to 240 V |
| 911401723482 | RC095V LED30S/865 PSU W12L120 Grey | 220 to 240 V | 911401723592 | RC095V LED13S/865 PSU W07L60 Black | 220 to 240 V |
| 911401723492 | RC095V LED15S/840 PSU W12L60 Black | 220 to 240 V | 911401723542 | RC095V LED26S/840 PSU W07L120 Grey | 220 to 240 V |
| 911401723502 | RC095V LED15S/840 PSU W12L60 Grey | 220 to 240 V | 911401723562 | RC095V LED26S/865 PSU W07L120 Grey | 220 to 240 V |
| 911401723522 | RC095V LED15S/865 PSU W12L60 Grey | 220 to 240 V | 911401723582 | RC095V LED13S/840 PSU W07L60 Grey | 220 to 240 V |
| 911401723692 | RC095V LED30S/830 PSU W12L120 Grey GM | 220 to 240 V | 911401723602 | RC095V LED13S/865 PSU W07L60 Grey | 220 to 240 V |
| 911401723702 | RC095V LED30S/840 PSU W12L120 Grey GM | 220 to 240 V | 911401723632 | RC095V LED26S/830 PSU W07L120 Black TW | 100 to 240 V |
| 911401723712 | RC095V LED30S/865 PSU W12L120 Grey GM | 220 to 240 V | 911401723642 | RC095V LED26S/830 PSU W07L120 Grey TW | 100 to 240 V |
| 911401723722 | RC095V LED15S/830 PSU W12L60 Grey GM | 220 to 240 V | 911401723652 | RC095V LED26S/840 PSU W07L120 Black TW | 100 to 240 V |
| 911401723732 | RC095V LED15S/840 PSU W12L60 Grey GM | 220 to 240 V | 911401723662 | RC095V LED26S/840 PSU W07L120 Grey TW | 100 to 240 V |
| 911401723742 | RC095V LED15S/865 PSU W12L60 Grey GM | 220 to 240 V | 911401723672 | RC095V LED26S/865 PSU W07L120 Black TW | 100 to 240 V |
| 911401723752 | RC095V LED30S/840 PSU W12L120 Grey RCA | 220-240 V | 911401723682 | RC095V LED26S/865 PSU W07L120 Grey TW | 100 to 240 V |

General Information

SmartBright Suspension

| Order Code | Full Product Name | Beam angle of light source |
|--------------|--|----------------------------|
| 911401723452 | RC095V LED30S/840 PSU W12L120 Black | - ° |
| 911401723472 | RC095V LED30S/865 PSU W12L120 Black | - ° |
| 911401723512 | RC095V LED15S/865 PSU W12L60 Black | - ° |
| 911401723462 | RC095V LED30S/840 PSU W12L120 Grey | - ° |
| 911401723482 | RC095V LED30S/865 PSU W12L120 Grey | - ° |
| 911401723492 | RC095V LED15S/840 PSU W12L60 Black | - ° |
| 911401723502 | RC095V LED15S/840 PSU W12L60 Grey | - ° |
| 911401723522 | RC095V LED15S/865 PSU W12L60 Grey | - ° |
| 911401723692 | RC095V LED30S/830 PSU W12L120 Grey GM | - ° |
| 911401723702 | RC095V LED30S/840 PSU W12L120 Grey GM | - ° |
| 911401723712 | RC095V LED30S/865 PSU W12L120 Grey GM | - ° |
| 911401723722 | RC095V LED15S/830 PSU W12L60 Grey GM | - ° |
| 911401723732 | RC095V LED15S/840 PSU W12L60 Grey GM | - ° |
| 911401723742 | RC095V LED15S/865 PSU W12L60 Grey GM | - ° |
| 911401723752 | RC095V LED30S/840 PSU W12L120 Grey RCA | - |

| Order Code | Full Product Name | Beam angle of light source |
|--------------|--|----------------------------|
| 911401723762 | RC095V LED30S/865 PSU W12L120 Grey RCA | - |
| 911401723532 | RC095V LED26S/840 PSU W07L120 Black | - ° |
| 911401723552 | RC095V LED26S/865 PSU W07L120 Black | - ° |
| 911401723572 | RC095V LED13S/840 PSU W07L60 Black | - ° |
| 911401723592 | RC095V LED13S/865 PSU W07L60 Black | - ° |
| 911401723542 | RC095V LED26S/840 PSU W07L120 Grey | - ° |
| 911401723562 | RC095V LED26S/865 PSU W07L120 Grey | - ° |
| 911401723582 | RC095V LED13S/840 PSU W07L60 Grey | - ° |
| 911401723602 | RC095V LED13S/865 PSU W07L60 Grey | - ° |
| 911401723632 | RC095V LED26S/830 PSU W07L120 Black TW | - ° |
| 911401723642 | RC095V LED26S/830 PSU W07L120 Grey TW | - ° |
| 911401723652 | RC095V LED26S/840 PSU W07L120 Black TW | - ° |
| 911401723662 | RC095V LED26S/840 PSU W07L120 Grey TW | - ° |
| 911401723672 | RC095V LED26S/865 PSU W07L120 Black TW | - ° |
| 911401723682 | RC095V LED26S/865 PSU W07L120 Grey TW | - ° |

Initial Performance (IEC Compliant) (1/2)

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|-------------------------------------|----------------------|-------------------------------|--------------------------------|-----------------------|
| 911401723452 | RC095V LED30S/840 PSU W12L120 Black | ≤5 | 4000 K | 88 lm/W | 3000 lm |
| 911401723472 | RC095V LED30S/865 PSU W12L120 Black | ≤5 | 6500 K | 88 lm/W | 3000 lm |
| 911401723512 | RC095V LED15S/865 PSU W12L60 Black | ≤5 | 6500 K | 88 lm/W | 1500 lm |
| 911401723462 | RC095V LED30S/840 PSU W12L120 Grey | ≤5 | 4000 K | 88 lm/W | 3000 lm |
| 911401723482 | RC095V LED30S/865 PSU W12L120 Grey | ≤5 | 6500 K | 88 lm/W | 1500 lm |
| 911401723492 | RC095V LED15S/840 PSU W12L60 Black | ≤5 | 6500 K | 88 lm/W | 3000 lm |
| 911401723502 | RC095V LED15S/840 PSU W12L60 Grey | ≤5 | 4000 K | 88 lm/W | 1500 lm |
| 911401723522 | RC095V LED15S/865 PSU W12L60 Grey | ≤5 | 6500 K | 88 lm/W | 1500 lm |

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|--|----------------------|-------------------------------|--------------------------------|-----------------------|
| 911401723452 | RC095V LED30S/840 PSU W12L120 Black | ≤5 | 4000 K | 88 lm/W | 3000 lm |
| 911401723472 | RC095V LED30S/865 PSU W12L120 Black | ≤5 | 6500 K | 88 lm/W | 3000 lm |
| 911401723512 | RC095V LED15S/865 PSU W12L60 Black | ≤5 | 6500 K | 88 lm/W | 1500 lm |
| 911401723462 | RC095V LED30S/840 PSU W12L120 Grey | ≤5 | 4000 K | 88 lm/W | 3000 lm |
| 911401723482 | RC095V LED30S/865 PSU W12L120 Grey | ≤5 | 6500 K | 88 lm/W | 1500 lm |
| 911401723492 | RC095V LED15S/840 PSU W12L60 Black | ≤5 | 6500 K | 88 lm/W | 3000 lm |
| 911401723502 | RC095V LED15S/840 PSU W12L60 Grey | ≤5 | 4000 K | 88 lm/W | 1500 lm |
| 911401723522 | RC095V LED15S/865 PSU W12L60 Grey | ≤5 | 6500 K | 88 lm/W | 1500 lm |
| 911401723692 | RC095V LED30S/830 PSU W12L120 Grey GM | ≤5 | 6500 K | 88 lm/W | 3000 lm |
| 911401723702 | RC095V LED30S/840 PSU W12L120 Grey GM | ≤5 | 3000 K | 88 lm/W | 3000 lm |
| 911401723712 | RC095V LED30S/865 PSU W12L120 Grey GM | ≤5 | 4000 K | 88 lm/W | 3000 lm |
| 911401723722 | RC095V LED15S/830 PSU W12L60 Grey GM | ≤5 | 6500 K | 88 lm/W | 3000 lm |
| 911401723732 | RC095V LED15S/840 PSU W12L60 Grey GM | ≤5 | 3000 K | 88 lm/W | 1500 lm |
| 911401723742 | RC095V LED15S/865 PSU W12L60 Grey GM | ≤5 | 4000 K | 88 lm/W | 1500 lm |
| 911401723752 | RC095V LED30S/840 PSU W12L120 Grey RCA | - | 4000 K | 88 lm/W | 3000 lm |

SmartBright Suspension

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|--|----------------------|-------------------------------|--------------------------------|-----------------------|
| 911401723762 | RC095V LED30S/865 PSU W12L120 Grey RCA | - | 6500 K | 88 lm/W | 3000 lm |
| 911401723532 | RC095V LED26S/840 PSU W07L120 Black | ≤5 | 4000 K | 93 lm/W | 2600 lm |
| 911401723552 | RC095V LED26S/865 PSU W07L120 Black | ≤5 | 6500 K | 93 lm/W | 2600 lm |
| 911401723572 | RC095V LED13S/840 PSU W07L60 Black | ≤5 | 4000 K | 93 lm/W | 1300 lm |
| 911401723592 | RC095V LED13S/865 PSU W07L60 Black | ≤5 | 6500 K | 93 lm/W | 1300 lm |
| 911401723542 | RC095V LED26S/840 PSU W07L120 Grey | ≤5 | 4000 K | 93 lm/W | 2600 lm |
| 911401723562 | RC095V LED26S/865 PSU W07L120 Grey | ≤5 | 6500 K | 93 lm/W | 2600 lm |
| 911401723582 | RC095V LED13S/840 | ≤5 | 4000 K | 93 lm/W | 1300 lm |

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|--|----------------------|-------------------------------|--------------------------------|-----------------------|
| | PSU W07L60 Grey | | | | |
| 911401723602 | RC095V LED13S/865 PSU W07L60 Grey | ≤5 | 6500 K | 93 lm/W | 1300 lm |
| 911401723632 | RC095V LED26S/830 PSU W07L120 Black TW | ≤5 | 3000 K | 93 lm/W | 2600 lm |
| 911401723642 | RC095V LED26S/830 PSU W07L120 Grey TW | ≤5 | 3000 K | 93 lm/W | 2600 lm |
| 911401723652 | RC095V LED26S/840 PSU W07L120 Black TW | ≤5 | 4000 K | 93 lm/W | 2600 lm |
| 911401723662 | RC095V LED26S/840 PSU W07L120 Grey TW | ≤5 | 4000 K | 93 lm/W | 2600 lm |
| 911401723672 | RC095V LED26S/865 PSU W07L120 Black TW | ≤5 | 6500 K | 93 lm/W | 2600 lm |
| 911401723682 | RC095V LED26S/865 PSU W07L120 Grey TW | ≤5 | 6500 K | 93 lm/W | 2600 lm |

Initial Performance (IEC Compliant) (2/2)

| Order Code | Full Product Name | Initial input power |
|--------------|--|---------------------|
| 911401723452 | RC095V LED30S/840 PSU W12L120 Black | 34 W |
| 911401723472 | RC095V LED30S/865 PSU W12L120 Black | 34 W |
| 911401723512 | RC095V LED15S/865 PSU W12L60 Black | 17 W |
| 911401723462 | RC095V LED30S/840 PSU W12L120 Grey | 34 W |
| 911401723482 | RC095V LED30S/865 PSU W12L120 Grey | 17 W |
| 911401723492 | RC095V LED15S/840 PSU W12L60 Black | 34 W |
| 911401723502 | RC095V LED15S/840 PSU W12L60 Grey | 17 W |
| 911401723522 | RC095V LED15S/865 PSU W12L60 Grey | 17 W |
| 911401723692 | RC095V LED30S/830 PSU W12L120 Grey GM | 34 W |
| 911401723702 | RC095V LED30S/840 PSU W12L120 Grey GM | 34 W |
| 911401723712 | RC095V LED30S/865 PSU W12L120 Grey GM | 34 W |
| 911401723722 | RC095V LED15S/830 PSU W12L60 Grey GM | 34 W |
| 911401723732 | RC095V LED15S/840 PSU W12L60 Grey GM | 17 W |
| 911401723742 | RC095V LED15S/865 PSU W12L60 Grey GM | 17 W |
| 911401723752 | RC095V LED30S/840 PSU W12L120 Grey RCA | 34 W |

| Order Code | Full Product Name | Initial input power |
|--------------|--|---------------------|
| 911401723762 | RC095V LED30S/865 PSU W12L120 Grey RCA | 34 W |
| 911401723532 | RC095V LED26S/840 PSU W07L120 Black | 28 W |
| 911401723552 | RC095V LED26S/865 PSU W07L120 Black | 28 W |
| 911401723572 | RC095V LED13S/840 PSU W07L60 Black | 14 W |
| 911401723592 | RC095V LED13S/865 PSU W07L60 Black | 14 W |
| 911401723542 | RC095V LED26S/840 PSU W07L120 Grey | 28 W |
| 911401723562 | RC095V LED26S/865 PSU W07L120 Grey | 28 W |
| 911401723582 | RC095V LED13S/840 PSU W07L60 Grey | 14 W |
| 911401723602 | RC095V LED13S/865 PSU W07L60 Grey | 14 W |
| 911401723632 | RC095V LED26S/830 PSU W07L120 Black TW | 28 W |
| 911401723642 | RC095V LED26S/830 PSU W07L120 Grey TW | 28 W |
| 911401723652 | RC095V LED26S/840 PSU W07L120 Black TW | 28 W |
| 911401723662 | RC095V LED26S/840 PSU W07L120 Grey TW | 28 W |
| 911401723672 | RC095V LED26S/865 PSU W07L120 Black TW | 28 W |
| 911401723682 | RC095V LED26S/865 PSU W07L120 Grey TW | 28 W |

Mechanical and Housing

| Order Code | Full Product Name | Color | Order Code | Full Product Name | Color |
|--------------|--|-------|--------------|--|-------|
| 911401723452 | RC095V LED30S/840 PSU W12L120 Black | black | 911401723762 | RC095V LED30S/865 PSU W12L120 Grey RCA | Gray |
| 911401723472 | RC095V LED30S/865 PSU W12L120 Black | black | 911401723532 | RC095V LED26S/840 PSU W07L120 Black | black |
| 911401723512 | RC095V LED15S/865 PSU W12L60 Black | black | 911401723552 | RC095V LED26S/865 PSU W07L120 Black | black |
| 911401723462 | RC095V LED30S/840 PSU W12L120 Grey | Gray | 911401723572 | RC095V LED13S/840 PSU W07L60 Black | black |
| 911401723482 | RC095V LED30S/865 PSU W12L120 Grey | Gray | 911401723592 | RC095V LED13S/865 PSU W07L60 Black | black |
| 911401723492 | RC095V LED15S/840 PSU W12L60 Black | Gray | 911401723542 | RC095V LED26S/840 PSU W07L120 Grey | Gray |
| 911401723502 | RC095V LED15S/840 PSU W12L60 Grey | Gray | 911401723562 | RC095V LED26S/865 PSU W07L120 Grey | Gray |
| 911401723522 | RC095V LED15S/865 PSU W12L60 Grey | Gray | 911401723582 | RC095V LED13S/840 PSU W07L60 Grey | Gray |
| 911401723692 | RC095V LED30S/830 PSU W12L120 Grey GM | Gray | 911401723602 | RC095V LED13S/865 PSU W07L60 Grey | Gray |
| 911401723702 | RC095V LED30S/840 PSU W12L120 Grey GM | Gray | 911401723632 | RC095V LED26S/830 PSU W07L120 Black TW | black |
| 911401723712 | RC095V LED30S/865 PSU W12L120 Grey GM | Gray | 911401723642 | RC095V LED26S/830 PSU W07L120 Grey TW | Gray |
| 911401723722 | RC095V LED15S/830 PSU W12L60 Grey GM | Gray | 911401723652 | RC095V LED26S/840 PSU W07L120 Black TW | black |
| 911401723732 | RC095V LED15S/840 PSU W12L60 Grey GM | Gray | 911401723662 | RC095V LED26S/840 PSU W07L120 Grey TW | Gray |
| 911401723742 | RC095V LED15S/865 PSU W12L60 Grey GM | Gray | 911401723672 | RC095V LED26S/865 PSU W07L120 Black TW | black |
| 911401723752 | RC095V LED30S/840 PSU W12L120 Grey RCA | Gray | 911401723682 | RC095V LED26S/865 PSU W07L120 Grey TW | Gray |

