



The coolest light, feels twice as bright

TL-D Snow White

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high color temperature of the Snow White range creates very cool ambiances, making the lamp especially suitable in very hot and dry climate conditions.

Benefits

- Generates a unique pleasantly cool snowy light, which is perfect for the creation of a very bright cool ambiance in all kind of applications
- The cool color makes you feel more comfortable and active, especially in hot and sunny climate conditions

Features

- Extreme cool light

Application

- Parking lots and covered car parks
- Industrial, warehouses, public areas
- Shops, offices
- Signage

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

TL-D Snow White

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W Snow White 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 36W Snow White 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D 58W Snow White 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

General Information	
Cap-Base	G13
Light Technical	
Chromaticity Coordinate X (Nom)	264
Chromaticity Coordinate Y (Nom)	280
Color Designation	Extreme Cool Daylight
Correlated Color Temperature (Nom)	12000 K
Color rendering index (CRI)	75
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

Light Technical

Order Code	Full Product Name	Luminous Flux
89350540	TL-D 18W Snow White 1SL/25	1,000 lm
89352940	TL-D 36W Snow White 1SL/25	2,370 lm
89354340	TL-D 58W Snow White 1SL/25	3,740 lm

Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
89350540	TL-D 18W Snow White 1SL/25	360 mA	59 V	18 W
89352940	TL-D 36W Snow White 1SL/25	440 mA	103 V	36 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
89354340	TL-D 58W Snow White 1SL/25	670 mA	111 V	58 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
89350540	TL-D 18W Snow White 1SL/25	22 kWh
89352940	TL-D 36W Snow White 1SL/25	43 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
89354340	TL-D 58W Snow White 1SL/25	68 kWh

TL-D Snow White

