



Trusted Performance, Everyday

SmartBright Highbay G3

SmartBright Highbay G3 is a high efficient and reliable LED luminaire. Designed as the point to point replacement for HPI 250W/400W luminaires, it offers customers all the benefits of LED lighting – reduced energy consumption, longer service time and less maintenance. In addition, with using high quality of the optical cover, it provides an excellent quality of light, which effectively improves the comfort of your environment.

Benefits

- Energy saving up to 65% comparing to HPI-P system
- · Comfort light quality
- · Safe & Reliable
- · Easy installation and retrofitting

Features

- · High efficacy: 100 lumens per watt
- · High quality optical cover ensure good uniformity
- \cdot Lifetime of 30,000 hours @ Ta35°C with end-to-end Philips production quality assurance
- Full family is in compliance with CB and EMC norms
- · Suitable for pole and hook mounting

Application

- Industry : Factories, warehouses, workshops, assembly lines, etc.
- · High ceiling indoor : Shopping malls, airports, stadium, etc.

SmartBright Highbay G3

Versions



BY239P LED200/CW PSU CAU

-			
Driver failure rate at 5000 h	0.01 %		
Application conditions			
Ambient temperature range	-20 to +45 °C		
Maximum dim level	Not applicable		
Suitable for random switching	No		
Approval and application			
Mech. impact protection code	IK06		
Ingress protection code	IP65		
Controls and dimming			
Dimmable	No		
Operating and electrical			
Input Voltage	220 to 240 V		
General information			
CE mark	CE mark		
Protection class IEC	Safety class I		
Optical cover/lens type	Opal		
Driver included	Yes		
ENEC mark	-		
Flammability mark	-		
Glow-wire test Light source replaceable	- No		
Number of gear units	1 unit		
Optic type	Symmetrical		
Optic type	Symmetrical		
Initial performance (IEC compliant)		
Init. Color Rendering Index	>80		
Luminous flux tolerance	+/-10%		
	, ,,,,,		
Mechanical and housing			
Color	Dark gray		

Initial performance (IEC compliant)

		Init. Corr. Color	Initial LED	Initial luminous	Initial input
Order Code	Full Product Name	Temperature	luminaire efficacy	flux	power
911401538261	BY239P LED150/CW	5000 K	104 lm/W	15000 lm	145 W
	PSU CAU				
911401538461	BY239P LED200/NW	4000 K	105 lm/W	20000 lm	190 W
	PSU CAU				

SmartBright Highbay G3



© 2022 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.