



# Provides soft, warm light and 3 wattage settings

# LED 3-Way

Philips LED A-shape light bulb provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

#### **Benefits**

- · Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistancy with high 80+ color rendering (CRI)
- $\cdot$  3-Way switching to get exactly the right amount of light when you need it

#### **Features**

- Light equivalent to 3 standard incandescent bulb outputs when used with a standard 3-way socket or luminaire
- 25,000-hour rated average life
- · Instant on
- · ENERGY STAR qualified
- Emits virtually no UV/IR light in the beam

### **Application**


- · Hotels/Motels
- Residential & Assisted Living

## Versions



Single Contact Medium Screw A21 (A21) Frosted

# Dimensional drawing



Product	D	С
18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	70.6 mm	133.1 mm
14A21/LED/927/P/E26/3WAY ND 4/1FB T20	70.6 mm	133.1 mm

#### **Controls and dimming** Dimmable No Operating and electrical Input Frequency 60 Hz Voltage (Nom) 120 V Starting Time (Nom) General information Cap-Base Switching Cycle 50000X Light technical Beam Angle (Nom) 250° Color Code 927 Correlated Color Temperature (Nom) 2700 K Color Rendering Index (Nom) 90 Llmf At End Of Nominal Lifetime 70 % (Nom) Mechanical and housing Bulb Finish Frosted Bulb Shape A21 (A21)

## Operating and electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Nom)
556928	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	100-60-40 W	14, 8, 5 W
556936	18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	150-100-50 W	18.5, 13, 6 W

## General information

# LED 3-Way

Order Code	Full Product Name	Nominal Lifetime (Nom)
556928	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	25000 h

Order Code	Full Product Name	Nominal Lifetime (Nom)
556936	18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	15000 h


## Light technical


Order Code	Full Product Name	Luminous Flux (Nom)
556928	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	1600-800-450 lm

Order Code	Full Product Name	Luminous Flux (Nom)
556936	18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	2150-1600-620 lm

# Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
556928	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	80 ℃
556936	18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	95 ℃







© 2022 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.