



The new Philips Smartbright slim panel offers exceptional value. It is Perfect for your everyday ceiling lighting installations. It is available in 3 standard sizes and 2 different CCT options to suit your need.

SmartBright Slim panel KR

The new Smartbright slim panel offers customer excellent solution for their lighting needs. It is durable, energy efficient and comes with 3 years warranty.

Benefits

SmartBright Slim panel KR

Features

Application

Versions



RC091V

RC091V

RC091V

Application Conditions	
Ambient temperature range	-10 to +40 °C
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
CE mark	-
Protection class IEC	Safety class I
Optical cover/lens type	Polystyrene bowl/ cover prismatic
Driver included	Yes
Initial Performance (IEC Compliant)	
Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Color	White

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401746872	RC091V LED45S/840 PSU W64L64 KR	840 neutral white	4000 K	90 lm/W	4500 lm
911401746892	RC091V LED45S/857 PSU W64L64 KR	857 daylight	5700 K	90 lm/W	4500 lm
911401746882	RC091V LED45S/840 PSU W32L128 KR	840 neutral white	4000 K	90 lm/W	4500 lm
911401746902	RC091V LED45S/857 PSU W32L128 KR	857 daylight	5700 K	90 lm/W	4500 lm
911401746912	RC091V LED20S/840 PSU W32L64 KR	840 neutral white	4000 K	80 lm/W	2000 lm
911401746922	RC091V LED20S/857 PSU W32L64 KR	857 daylight	5700 K	80 lm/W	2000 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
911401746872	RC091V LED45S/840 PSU W64L64 KR	50 W
911401746892	RC091V LED45S/857 PSU W64L64 KR	50 W

Order Code	Full Product Name	Initial input power
911401746882	RC091V LED45S/840 PSU W32L128 KR	50 W
911401746902	RC091V LED45S/857 PSU W32L128 KR	50 W

SmartBright Slim panel KR

Order Code	Full Product Name	Initial input power	Order Code	Full Product Name	Initial input power
911401746912	RC091V LED20S/840 PSU W32L64 KR	25 W	911401746922	RC091V LED20S/857 PSU W32L64 KR	25 W

