



Smartbright Waterproof Batten G3 provide flexibility to customer to choose from 3 sizes, standard and through wiring version and 2 CCTs to cater to different customer needs

Smartbright Waterproof G3 WT068C

Philips Smartbright Waterproof G3 batten offers exceptional value. It is Perfect for everyday lighting installations. Available in 3 standard sizes, it has option of Standard and through wiring version.

Benefits

- Lifetime: 30,000 hrs @ L70B50, 3 Years warranty
- IP66, IK06
- Quick connector for easy installation

Smartbright Waterproof G3 WT068C

Features

- 2 colour temperatures, 3 sizes and Standard and through wiring version
- IP66/IK06 – Water and dustproof. For all weather
- Reliable with a long service life of 30 000 hours L70
- 3 years warranty
- Quick connector for easy installation

Application

- Parking Garages
- Offices

Versions




Smartbright Waterproof G3


Smartbright Waterproof G3

Dimensional drawing


WT068C TW-4ft



WT068C TW-2ft



WT068C TW-5ft



Smartbright Waterproof G3 WT068C

General Information	
CE mark	CE mark
Light Technical	
Optical cover type	-
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	110 lm/W
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White and gray
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK06
Ingress protection code	IP66
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux
911401882180	WT068C CW LED56 L1500 PSU TW1	6500 K	5,600 lumen
911401882480	WT068C NW LED56 L1500 PSU TW1	4000 K	5,600 lumen
911401882080	WT068C CW LED36 L1200 PSU TW1	6500 K	3,600 lumen
911401882380	WT068C NW LED36 L1200 PSU TW1	4000 K	3,600 lumen
911401881980	WT068C CW LED18 L600 PSU TW1	6500 K	1,800 lumen
911401882280	WT068C NW LED18 L600 PSU TW1	4000 K	1,800 lumen

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401882180	WT068C CW LED56 L1500 PSU TW1	51 W
911401882480	WT068C NW LED56 L1500 PSU TW1	51 W
911401882080	WT068C CW LED36 L1200 PSU TW1	33 W

Order Code	Full Product Name	Power Consumption
911401882380	WT068C NW LED36 L1200 PSU TW1	33 W
911401881980	WT068C CW LED18 L600 PSU TW1	16.5 W
911401882280	WT068C NW LED18 L600 PSU TW1	16.5 W

