

Tango G2 LED

BVP283 LED192/WW 210W 220-240V AWBE

Tango G2 LED, 19200 lm, 210 W, 730 warm white, Safety class I

Tango G2 LED is a general purpose LED flood lighting luminiare for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data

General Information	
Driver included	Yes
Lighting Technology	LED
CE mark	CE mark
Light Technical	
Luminous Flux	19,200 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	>70
Light source color	730 warm white
Optical cover type	Glass
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Power Consumption	210 W
Power Factor (Fraction)	0.95

Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Aluminum and gray
Overall length	480 mm
Overall width	655 mm
Overall height	60 mm


Datasheet, 2023, October 26 data subject to change

Tango G2 LED

Dimensions (Height x Width x Depth)	60 x 655 x 480 mm	
Approval and Application		
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]	
Mech. impact protection code	IK07 [2 J reinforced]	
Protection class IEC	Safety class I	
Initial Performance (IEC Compliant)		
Luminous flux tolerance	+/-10%	
Power consumption tolerance	+/-10%	

Product Data	
Order product name	BVP283 LED192/WW 210W 220-240V AWBE
Full product name	BVP283 LED192/WW 210W 220-240V AWBE
Full product code	911401605303
Order code	911401605303
Material Nr. (12NC)	911401605303
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.