



Tango G2 LED

BVP283 LED256/WW 280W 220-240V SWB

Tango G2 LED, 25600 lm, 280 W, 740 neutral white, Safety class I

Tango G2 LED is a general purpose LED flood lighting luminiare for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data

General Information	
Driver included	Yes
Lighting Technology	LED
CE mark	CE mark
Light Technical	
Luminous Flux	25,600 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Glass
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz

Power Consumption	280 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Temperature	
Ambient temperature range	-40 to +50 ℃
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate

Datasheet, 2023, May 16 data subject to change

Tango G2 LED

Housing Color	Aluminum and gray	
Overall length	480 mm	
Overall width	655 mm	
Overall height	60 mm	
Dimensions (Height x Width x Depth)	60 x 655 x 480 mm	
Approval and Application		
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]	
Mech. impact protection code	IK07 [2 J reinforced]	
Protection class IEC	Safety class I	
Initial Performance (IEC Compliant)		

+/-10%

Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP283 LED256/WW 280W 220-240V SWB
Full product name	BVP283 LED256/WW 280W 220-240V SWB
Full product code	911401668802
Order code	911401668802
Material Nr. (12NC)	911401668802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
radiiciator i acia per outer box	<u>'</u>

Dimensional drawing

Luminous flux tolerance



