PHILIPS

Lighting



Coreline Slim Batten

BN126C LED41S/840 PSU L1200

Coreline Slim Batten, 31 W, 4100 lm, 4000 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Product data

General Information	
Light source engine type	LED
CE mark	CE mark

Light Technical	
Luminous Flux	4,100 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optical cover type	Polycarbonate Diffuser

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	31 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	45

Temperature	
Ambient temperature range	-20 to +40 °C

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Steel
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Opal
Overall length	1,135 mm
Overall width	65 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 65 x 1135 mm

Approval and Application	
Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
Mech. impact protection code	IK04 [0.5 J standard plus]

Coreline Slim Batten


Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	BN126C LED41S/840 PSU L1200
Full product name	BN126C LED41S/840 PSU L1200
Full product code	692382863853599

Order code	911401898980
Material Nr. (12NC)	911401898980
Local order code	BN12641L8404FT
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638535
Numerator - Packs per outer box	8
EAN/UPC - Case	6923828638597

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.