

CityCurve gen2

BSP295 GRN29/740 PSR WSO II GR-900

CityCurve gen 2, LED GreenLine 2900 lm, 740 neutral white, Power supply unit regulating, Safety class II, Wide street optic

Offering a contemporary interpretation of the old 'bell'-shaped street light, CityCurve gen2, with its retro appearance, fits both modern urban spaces as well as historical environments. Its LED module allows cities to focus on reducing energy consumption. Designed for installation at heights of 4 to 6 meters, and offering a wide choice of brackets and columns, CityCurve gen2 is ideal for lighting urban centers and streets, pedestrian areas, squares and parks.

Product data

General Information	
Lamp family code	GRN29 [LED GreenLine 2900 lm]
Light source replaceable	Yes
Driver included	Yes
Product family code	BSP295 [CityCurve gen 2]
Lighting Technology	LED
CE mark	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s

Light Technical	
Luminous Flux	2,372 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	81.8 lm/W
Number of light sources	24
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover clear
Optic type outdoor	Wide street optic

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	29 W

Temperature	
Ambient temperature range	-25 to +35 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating

Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	Polycarbonate

CityCurve gen2

Mounting device	Spigot

Approval and Application


Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class II

Product Data

Order product name	BSP295 GRN29/740 PSR WSO II GR-900
Full product name	BSP295 GRN29/740 PSR WSO II GR-900

Full product code	871794312023900
Order code	12023900
Material Nr. (12NC)	912300020024
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943120239
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943120239

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.