



# 鹵素反射燈

## 6423FO 150W GZ6.35 15V 1CT/10X5F

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

### 产品数据


| 一般資訊              |                 |
|-------------------|-----------------|
| 燈座基底              | GZ6.35 [GZ6.35] |
| 操作位置              | P90/P15         |
| 壽命 (故障率 50%) (標稱) | 50 h            |
| 照明技術              |                 |
| 光通量               | 840 lm          |
| 相關色彩溫度 (規範)       | 3380 K          |
| 演色性指數 (CRI)       | 100             |
| 運轉與電力             |                 |
| 耗電量               | 150 W           |
| 電壓 (標稱)           | 15 V            |
| 電壓 (標稱)           | 15 V            |

| 控制與調光           |                                  |
|-----------------|----------------------------------|
| 可調光             | 是                                |
| 機械與外罩           |                                  |
| 燈泡材質            | 石英-UV 開放式                        |
| 反射罩表層           | -                                |
| 燈泡形狀            | R50 [R 50mm]                     |
| 產品資料            |                                  |
| 下訂產品名稱          | 6423FO 150W GZ6.35 15V 1CT/10X5F |
| 完整產品名稱          | 6423FO 150W GZ6.35 15V 1CT/10X5F |
| 完整產品代碼          | 871150040971360                  |
| 訂單代碼            | 924048218504                     |
| 材質 Nr. (12NC)   | 924048218504                     |
| 分子 - 每個包裝的數量    | 1                                |
| EAN/UPC - 產品/案例 | 8711500409713                    |

鹵素反射燈

|             |               |
|-------------|---------------|
| 分子 - 每一外盒包裝 | 50            |
| EAN/UPC - 箱 | 8711500419231 |

二维绘图



| Product                          | D (max) | C (max) |
|----------------------------------|---------|---------|
| 6423FO 150W GZ6.35 15V 1CT/10X5F | 50 mm   | 42 mm   |

