



# **TUV PL-S**

## TUV PL-S 9W/2P 1CT/6X10BOX

TUV PL-S lamps are compact UVC (germicidal) lamps used in residential water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-S lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

#### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

#### **Product data**


General Information		Voltage (Nom)	60 V		
Cap-Base	G23				
Useful Life (Nom)	9,000 h	Mechanical and Housing	Mechanical and Housing		
		Bulb Shape	2XT12		
Light Technical					
Color Code	TUV	Approval and Application			
Color Designation	- [Not Specified]	Mercury (Hg) Content (Nom) 3.0 mg			
Depreciation at Useful Lifetime	20 %				
		UV			
Operating and Electrical		UV-C Radiation at 100 hr	2.5 W		
Power Consumption	8.6 W				
Lamp Current (Nom)	0.17 A	Product Data			
Voltage (Nom)	60 V	Order product name	TUV PL-S 9W/2P 1CT/6X10BOX		
		Full product name	TUV PL-S 9W/2P 1CT/6X10BOX		

### **TUV PL-S**

Full product code	871150061824580		
Local code description	TUVPLS9W		
Order code	927901704007		
Material Nr. (12NC)	927901704007		
Local order code	TUVPLS9W		
Numerator - Quantity Per Pack	1		


EAN/UPC - Product/Case	8711500618245		
Numerator - Packs per outer box	60		
EAN/UPC - Case	8711500618269		

#### Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-S 9W/2P 1CT/6X10BOX	13 mm	28 mm	129 mm	144.5 mm	167 mm

#### Photometric data



Spectral Power Distribution Colour - TUV PL-S 9W/2P 1CT/6X10BOX



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.