



# MASTER PL-L 4 Pin

## MASTER PL-L 18W/865/4P 1CT/25

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 2 parallel fluorescent tubes

### Product data

General Information	
Cap base	2G11 [ 2G11]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	15000 h
Life to 50% failures preheat (nom.)	20000 h
System description	na [-]
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	96 %
LSF 8000 h Rated	94 %
LSF 12000 h Rated	80 %
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	98 %
LSF Preheat 8000 h Rated	97 %
LSF Preheat 16000 h Rated	82 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Colour code	865 [ CCT of 6,500 K]
Luminous flux (nom.)	1200 lm
Luminous flux (rated) (nom.)	1170 lm
Colour designation	Cool Daylight
Correlated colour temperature (nom.)	6500 K
Luminous efficacy (rated) (nom.)	65 lm/W

Color rendering index (nom.)	80
LLMF 2000 h Rated	93 %
LLMF 4000 h Rated	91 %
LLMF 6000 h Rated	90 %
LLMF 8000 h Rated	89 %
LLMF 12000 h Rated	87 %
LLMF 16000 h Rated	88 %
LLMF 20000 h Rated	87 %

### Operating and Electrical

Power (Rated) (Nom)	18.0 W
Lamp current (nom.)	0.375 A

### Temperature

Design temperature (nom.)	30 °C
---------------------------	-------

### Controls and Dimming

Dimmable	yes
----------	-----

### Mechanical and Housing

Cap base information	4P
----------------------	----

### Approval and Application

Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg


# MASTER PL-L 4 Pin

Energy Consumption kWh/1000 h	20 kWh
<b>Product Data</b>	
Full product code	871150063514340
Order product name	MASTER PL-L 18W/865/4P 1CT/25
EAN/UPC – product	8711500635143
Order code	63514340
Local Code	18PLL865

Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	927903086572
Net weight (piece)	60.900 g
ILCOS Code	FSD-18/65/1B-E-2G11

## Warnings and Safety


### Dimensional drawing




PL-L 18W/865/4P

**Product**  
MASTER PL-L 18W/865/4P 1CT/25

### Photometric data



Lightcolour /865



Lightcolour /865

## MASTER PL-L 4 Pin

