



MASTER PL-L 4 Pin



MASTER PL-L 36W/830/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous Efficacy (rated) (Nom)		81 lm/W
Cap-Base	2G11	Color rendering index (CRI)	82	
Flux measurement reference	Sphere	Operating and Electrical		
Life to 50% Failures (Nom)	15,000 hour(s)	Power Consumption	36.3 W	
Light Technical		Lamp Current (Nom)	0.435 A	
Color Code	830 [CCT of 3000K]	Controls and Dimming		
Luminous Flux	2,850 lm	Dimmable	Yes	
Color Designation	Warm White (WW)	Approval and Application		
Chromaticity Coordinate X (Nom)	0.44	Energy Efficiency Class	G	
Chromaticity Coordinate Y (Nom)	0.403			
Correlated Color Temperature (Nom)	3000 K			

MASTER PL-L 4 Pin


Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	37 kWh
EPREL Registration Number	423270

Product Data

Order product name	MASTER PL-L 36W/830/4P 1CT/25
Full product name	MASTER PL-L 36W/830/4P 1CT/25
Full product code	871150070674440


Order code	927903408370
Material Nr. (12NC)	927903408370
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500706744
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500710888

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 36W/830/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/830/4P 1CT/25

