



MASTER PL-L Xtra 4 Pin



MASTER PL-L XTRA 36W/830/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2G11
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	21,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	2,800 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	81 lm/W
Color rendering index (CRI)	82


Operating and Electrical	
Power Consumption	36.3 W
Lamp Current (Nom)	0.435 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	3 mg
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	37 kWh
EPREL Registration Number	423276

MASTER PL-L Xtra 4 Pin

Product Data	
Order product name	MASTER PL-L Xtra 36W/830/4P 1CT/25
Full product name	MASTER PL-L XTRA 36W/830/4P 1CT/25
Full product code	871150089758940
Order code	89758940
Material Nr. (12NC)	927904783014


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500897589
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500897596

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L Xtra 36W/830/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L Xtra 36W/830/4P 1CT/25

