



MASTER PL-C 2 Pin

MASTER PL-C 13W/830/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

Product data

| General Information | |
|--------------------------------------|-----------------------|
| Cap base | G24D-1 [G24d-1] |
| Life to 10% failures (nom.) | 6500 h |
| Life to 50% failures (nom.) | 10000 h |
| LSF 2000 h Rated | 99 % |
| LSF 4000 h Rated | 98 % |
| LSF 6000 h Rated | 92 % |
| LSF 8000 h Rated | 78 % |
| Light Technical | |
| Colour Code | 830 [CCT of 3,000 K] |
| Lamp Luminous Flux 25°C EL (Nom) | 925 lm |
| Lamp Luminous Flux (Nom) | 925 lm |
| Colour Designation | Warm white (WW) |
| Colour Temperature, horizontal (Nom) | 3000 K |
| Lamp Luminous Efficacy EM (Nom) | 69 lm/W |
| Colour Rendering Index, horiz (Nom) | 82 |
| LLMF 2000 h Rated | 92 % |
| LLMF 4000 h Rated | 87 % |
| LLMF 6000 h Rated | 83 % |
| LLMF 8000 h Rated | 81 % |
| Operating and Electrical | |
| Power (Rated) (Nom) | 13.4 W |

| Lamp current (nom.) | 0.170 A |
|---------------------------------|------------------------------------|
| Temperature | |
| Design temperature (nom.) | 28 °C |
| Controls and Dimming | |
| Dimmable | no |
| Mechanical and Housing | |
| Cap base information | 2P |
| Approval and Application | |
| Energy efficiency label (EEL) | A |
| Mercury (Hg) content (nom.) | 1.4 mg |
| Energy Consumption kWh/1000 h | 17 kWh |
| Product Data | |
| Full product code | 871150026922500 |
| Order product name | MASTER PL-C 13W/830/2P 1CT/5X10BOX |
| EAN/UPC – product | 8711500269225 |
| Order code | 927904883001 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 50 |
| Material no. (12NC) | 927904883001 |
| Net weight (piece) | 53.600 g |


MASTER PL-C 2 Pin

ILCOS Code

FSQ-13/30/1B-I-G24d-1

Warnings and Safety



Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|---------------------------------------|---------|----------|---------|----------|----------|
| MASTER PL-C 13W/830/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |

PL-C 13W/830/2P


Photometric data



Lightcolour /830

Lightcolour /830

Lifetime



LDLE_PLC2P_0001-Life expectancy diagram

LDLE_PLC2P_0002-Life expectancy diagram

MASTER PL-C 2 Pin

Lifetime



LDLM_PLC2P_0001-Lumen maintenance diagram

