



# MASTER PL-C 2 Pin 2-針腳型

## MASTER PL-C 26W/827/2P 1CT/5X10BOX

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 4 個平行細長螢光燈管

### 安全提示

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

| 一般資訊               |                    |
|--------------------|--------------------|
| 燈座基底               | G24d-3             |
| 壽命 (故障率 50 %) (標稱) | 10,000 h           |
| 照明技術               |                    |
| 色碼                 | 827 [CCT of 2700K] |
| 光通量                | 1,800 lm           |
| 色彩名稱               | 白熾白色               |
| 相關色彩溫度 (規範)        | 2700 K             |
| 光效 (額定) (標準)       | 68 lm/W            |
| 演色性指數 (CRI)        | 82                 |
| 運轉與電力              |                    |
| 耗電量                | 26.5 W             |


| 燈具電流 (標稱)       | 0.335 A                            |
|-----------------|------------------------------------|
| 控制與調光           |                                    |
| 可調光             | 否                                  |
| 認證與應用           |                                    |
| 汞 (Hg) 含量 (標稱)  | 1.4 mg                             |
| 能源消耗 kWh/1000 h | 32 kWh                             |
| 產品資料            |                                    |
| 下訂產品名稱          | MASTER PL-C 26W/827/2P 1CT/5X10BOX |
| 完整產品名稱          | MASTER PL-C 26W/827/2P 1CT/5X10BOX |
| 完整產品代碼          | 871150062095800                    |
| 訂單代碼            | 927906182701                       |
| 材質 Nr. (12NC)   | 927906182701                       |

MASTER PL-C 2 Pin 2-针脚型

|                 |               |
|-----------------|---------------|
| 分子 - 每個包裝的數量    | 1             |
| EAN/UPC - 產品/案例 | 8711500620958 |
| 分子 - 每一外盒包裝     | 50            |


|             |               |
|-------------|---------------|
| EAN/UPC - 箱 | 8711500621276 |
|-------------|---------------|

二维绘图




| Product                            | D (max) | D1 (max) | A (max)  | B (max)  | C (max)  |
|------------------------------------|---------|----------|----------|----------|----------|
| MASTER PL-C 26W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm  | 130.5 mm | 149.0 mm | 171.4 mm |

光度数据




Spectral Power Distribution Colour - MASTER PL-C 26W/827/2P 1CT/5X10BOX

壽命



Life Expectancy Diagram - MASTER PL-C 26W/827/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-C 26W/827/2P 1CT/5X10BOX

MASTER PL-C 2 Pin 2-針腳型

壽命

Life Expectancy Diagram - MASTER PL-C 26W/827/2P 1CT/5X10BOX

