



# MASTER PL-C 2 Pin

## MASTER PL-C 26W/865/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G24d-3		66 lm/W
Flux measurement reference	Sphere	Color rendering index (CRI)	80
Life to 50% Failures (Nom)	10,000 hour(s)	<b>Operating and Electrical</b>	
<b>Light Technical</b>		Power Consumption	26.5 W
Color Code	865 [CCT of 6500K]	Lamp Current (Nom)	0.335 A
Luminous Flux	1,740 lm	<b>Controls and Dimming</b>	
Color Designation	Cool Daylight	Dimmable	No
Chromaticity Coordinate X (Nom)	0.313	<b>Approval and Application</b>	
Chromaticity Coordinate Y (Nom)	0.337	Energy Efficiency Class	G
Correlated Color Temperature (Nom)	6500 K		

# MASTER PL-C 2 Pin


Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	27 kWh
EPREL Registration Number	423289

## Product Data

Order product name	MASTER PL-C 26W/865/2P 1CT/5X10BOX
Full product name	MASTER PL-C 26W/865/2P 1CT/5X10BOX
Full product code	871150063531070


Order code	927906186540
Material Nr. (12NC)	927906186540
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500635310
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500716002

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/865/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm


## Photometric data



Spectral Power Distribution Colour - MASTER PL-C 26W/865/2P 1CT/5X10BOX

# MASTER PL-C 2 Pin

## Lifetime



Life Expectancy Diagram - MASTER PL-C 26W/865/2P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-C 26W/865/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-C 26W/865/2P 1CT/5X10BOX

