



MASTER PL-C 4 Pin

MASTER PL-C 13W/840/4P 1CT/5X10BOX

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 4 個平行細長螢光燈管

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般資訊	
燈座基底	G24q-1
照明技術	
色碼	840 [CCT of 4000K]
光通量	925 lm
色彩名稱	冷白光 (CW)
相關色彩溫度 (規範)	4000 K
光效 (額定) (標準)	69 lm/W
演色性指數 (CRI)	82
運轉與電力	
耗電量	13.0 W
燈具電流 (標稱)	0.170 A
控制與調光	
可調光	是

認證與應用	
汞 (Hg) 含量 (標稱)	1.4 mg
能源消耗 kWh/1000 h	15 kWh
產品資料	
下訂產品名稱	MASTER PL-C 13W/840/4P 1CT/5X10BOX
完整產品名稱	MASTER PL-C 13W/840/4P 1CT/5X10BOX
完整產品代碼	871150062332400
訂單代碼	927907184002
材質 Nr. (12NC)	927907184002
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500623324
分子 - 每一外盒包裝	50
EAN/UPC - 箱	8711500715739


MASTER PL-C 4 Pin

二维绘图




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm

光度数据




Spectral Power Distribution Colour - MASTER PL-C 13W/840/4P 1CT/5X10BOX

寿命




Life Expectancy Diagram - MASTER PL-C 13W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 13W/840/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

壽命



Lumen Maintenance Diagram - MASTER PL-C 13W/840/4P 1CT/5X10BOX

