



MASTER PL-C 4 Pin

MASTER PL-C 26W/865/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Product data

General Information	
Cap-Base	G24Q-3 [G24q-3]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux (Nom)	1740 lm
Luminous Flux (Rated) (Nom)	1740 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	66 lm/W
Color Rendering Index (Nom)	80
LLMF 2000 h Rated	90 %
LLMF 4000 h Rated	85 %
LLMF 6000 h Rated	81 %
LLMF 8000 h Rated	77 %

Operating and Electrical	
Power (Rated) (Nom)	26.0 W
Lamp Current (Nom)	0.335 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	29 kWh
Product Data	
Full product code	871150027705300
Order product name	MASTER PL-C 26W/865/4P 1CT/5X10BOX


MASTER PL-C 4 Pin

EAN/UPC - Product	8711500277053
Order code	927907386501
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50

Material Nr. (12NC)	927907386501
Net Weight (Piece)	60.400 g

Warnings and Safety


Dimensional drawing




PL-C 26W/865/4P

Product	MASTER PL-C 26W/865/4P 1CT/5X10BOX
---------	------------------------------------

Photometric data




Lightcolor /865




Lightcolor /865

Lifetime



Life Expectancy 3 h cycle



Life Expectancy 12 h cycle

MASTER PL-C 4 Pin

Lifetime



Lumen Maintenance 3 h and 12 h cycle

