



# Actinic BL PL-L Secura

## PL-L 36W/10/4P SECURA 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL PL-L Secura lamps are perfect for attracting insects. With the compact PL-L product format in a variety of wattages, new attractive designs are possible. Furthermore, these lamps have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		UV Depreciation at 5000 h	
Cap-Base	2G11 [ 2G11]		40 %
Main Application	Insect traps	Operating and Electrical	
Life to 50% Failures (Nom)	10000 h	Power (Nom)	36 W
		Lamp Current (Nom)	0.440 A
Light Technical		Voltage (Nom)	108 V
Color Code	10	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	228	Cap-Base Information	4 Pins
Chromaticity Coordinate Y (Nom)	215		
UV Depreciation at 2000 h	20 %		

# Actinic BL PL-L Secura

## Approval and Application

Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	1.8 mg

## UV


UV-A Radiation 100Hr (IEC)	7.7 W
----------------------------	-------

## Product Data

Full product code	871829119443900
-------------------	-----------------

Order product name	PL-L 36W/10/4P SECURA 1CT/25
EAN/UPC - Product	8718291194439
Order code	927909121001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927909121001
Net Weight (Piece)	133.000 g


## Dimensional drawing




PL-L 36W/10/4P SECURA

Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
PL-L 36W/10/4P	27 mm	40 mm	20.0	404.2 mm	430.0 mm	436.6 mm
SECURA 1CT/25			mm			

## Photometric data



XDPB\_XURPLL\_0001-Spectral power distribution B/W



XDPO\_XURPLL\_0001-Spectral power distribution Colour

