# **PHILIPS** Lighting



# Actinic BL PL-L Secura

## PL-L 36W/10/4P SECURA 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL PL-L Secura lamps are perfect for attracting insects. With the compact PL-L product format in a variety of wattages, new attactive designs are possible. Furthermore, these lamps have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

#### Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### **Product data**


General Information		<b>Operating and Electrical</b>	
Cap-Base	2G11	Power Consumption	36 W
Life to 50% Failures (Nom)	10,000 hour(s)	Lamp Current (Nom)	0.440 A
		Voltage (Nom)	108 V
Light Technical		Voltage (Nom)	108 V
Color Code	10		
Chromaticity Coordinate X (Nom)	228	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	215	Bulb Shape	2xT16
UV Depreciation at 2000 h	20 %		
UV Depreciation at 5000 h	40 %	Approval and Application	
		Mercury (Hg) Content (Max)	2.0 mg

### Actinic BL PL-L Secura

Mercury (Hg) Content (Nom)	2		
UV			
UV-A Radiation 100Hr (IEC)	7.7 W		
Product Data			
Order product name	PL-L 36W/10/4P SECURA 1CT/25		
Full product name	PL-L 36W/10/4P SECURA 1CT/25		
Full product code	871829119443900		


Order code	927909121001		
Material Nr. (12NC)	927909121001		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8718291194439		
Numerator - Packs per outer box	25		
EAN/UPC - Case	8718291194446		

#### **Dimensional drawing**



Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
PL-L 36W/10/4P	27 mm	40 mm	20.0 mm	404.2 mm	430.0 mm	436.6 mm
SECURA 1CT/25						

#### Photometric data



Spectral Power Distribution Colour - PL-L 36W/10/4P SECURA 1CT/25



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.