

MASTER PL-T TOP 4 Pin

MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	GX24Q-3 [GX24q-3]
Flux measurement reference	Sphere

Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,300 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	75 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Power Consumption	34.5 W
Lamp Current (Nom)	0.320 A

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	35 kWh
EPREL Registration Number	423329

MASTER PL-T TOP 4 Pin

Product Data	
Order product name	MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX
Full product code	871150056026170
Order code	927911984069
Material Nr. (12NC)	927911984069


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500560261
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500610034

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX	41 mm	98.7 mm	123.0 mm	138.7 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX

Lifetime




Lumen Maintenance Diagram - MASTER PL-T TOP 32W/840/4P 1CT/ 5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX

MASTER PL-T TOP 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.