



PL-T Triple 4-Pin Base

PL-T 57W/841/A/4P

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

General Information		LLMF 8000 h Rated		LLMF 12000 h Rated	
Base	GX24Q-5 [GX24q-5]		84 %		
Life to 50% Failures Preheat (Nom)	13000 h				
LSF Preheat 2000 h Rated	99 %	Operating and Electrical			
LSF Preheat 4000 h Rated	98 %	Power (Rated) (Nom)	51.0 W		
LSF Preheat 6000 h Rated	97 %	Lamp Current (Nom)	0.320 A		
LSF Preheat 8000 h Rated	90 %	Temperature			
Light Technical		Design Temperature (Nom)	28 °C		
Color Code	841 [CCT of 4100K]	Controls and Dimming			
Initial lumen (Nom)	4300 lm	Dimmable	Yes		
Luminous Flux (Rated) (Nom)	3900 lm	Mechanical and Housing			
Color Designation	Cool White (CW)	Cap-Base Information	4P		
Correlated Color Temperature (Nom)	4100 K	Approval and Application			
Luminous Efficacy (Rated) (Min)	76 lm/W	Energy Efficiency Label (EEL)	B		
Color Rendering Index (Nom)	82				
LLMF 2000 h Rated	92 %				
LLMF 4000 h Rated	88 %				
LLMF 6000 h Rated	85 %				


PL-T Triple 4-Pin Base

Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 57W/841/A/4P
EAN/UPC - Product	046677146337
Order code	146332
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	927914084020
Net Weight (Piece)	101.000 g
ILCOS Code	FSM-57/40/1B-E-GX24q=5

Warnings and Safety


Dimensional drawing




PL-T ALTO 57W/841/4P A

Product	D (max)	A (max)	B (max)	C (max)
PL-T 57W/841/A/4P	41 mm	157.7 mm	182.0 mm	197.7 mm

Lifetime



LDLM_PLTTOP4P_0001-Lumen maintenance diagram



LDLE_PLTTOP4P_0001-Life expectancy diagram

PL-T Triple 4-Pin Base

Lifetime



LDLE_PLTTOP4P_0002-Life expectancy diagram

