



MASTER PL-T 2 Pin

MASTER PL-T 26W/830/2P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	GX24D-3 [GX24d-3]	Power Consumption	26.9 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.335 A
Life to 50% Failures (Nom)	10,000 h		
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	No
Luminous Flux	1,800 lm		
Color Designation	Warm White (WW)	Approval and Application	
Chromaticity Coordinate X (Nom)	0.44	Energy Efficiency Class	G
Chromaticity Coordinate Y (Nom)	0.403	Mercury (Hg) Content (Max)	1.4 mg
Correlated Color Temperature (Nom)	3000 K	Mercury (Hg) Content (Nom)	1.4 mg
Luminous Efficacy (Rated) (Min)	66 lm/W	Energy Consumption kWh/1000 h	27 kWh
Color rendering index (CRI)	80	EPREL Registration Number	423344
		Product Data	
		Order product name	MASTER PL-T 26W/830/2P 1CT/5X10BOX

MASTER PL-T 2 Pin

Full product name	MASTER PL-T 26W/830/2P 1CT/5X10BOX
Full product code	871150061102470
Local code description	PLT26W8302P
Order code	927914583071
Material Nr. (12NC)	927914583071
Local order code	PLT26W8302P


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500611024
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500611109

Dimensional drawing





Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 26W/830/2P 1CT/5X10BOX	41 mm	86.7 mm	111.0 mm	134.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-T 26W/830/2P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-T 26W/830/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-T 26W/830/2P 1CT/5X10BOX

MASTER PL-T 2 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-T 26W/830/2P 1CT/5X10BOX

