PHILIPS

Lighting



MASTER TL-D Super 80

MASTER TL-D SUPER 80 36W/840 UNP/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	15,000 h

Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	3,350 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	93 lm/W
Colour rendering index (CRI)	80

Operating and Electrical	
Power Consumption	36.8 W
Lamp current (nom.)	0.440 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb shape	T8 [26 mm (T8)]

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.7 mg
Energy consumption kWh/1,000 hours	37 kWh
EPREL registration number	423384


Product Data	
Order product name	MASTER TL-D Super 80 36W/840 UNP/25
Full product name	MASTER TL-D SUPER 80 36W/840 UNP/25
Full EOC	871150061018840
Order code	61018840
Material no. (12 NC)	927921084069
Local order code	36840IP

MASTER TL-D Super 80

SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8711500610188
Numerator – packs per outer box	25


EAN/UPC - Case	8711500632494

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 36W/840 UNP/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Super 80 36W/840 UNP/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Super 80 36W/840 UNP/25



Life Expectancy Diagram - MASTER TL-D Super 80 36W/840 UNP/25

MASTER TL-D Super 80

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 36W/840 UNP/25

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.