



MASTER TL5 High Efficiency

MASTER TL5 HE 21W/865 SLV/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5
Features	na [Not Applicable]
Flux measurement reference	Sphere
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	1,750 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	0.313
Chromaticity Coordinate Y (Nom)	0.337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	84 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	20.8 W
Lamp Current (Nom)	0.165 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	21 kWh
EPREL Registration Number	423456

MASTER TL5 High Efficiency

Product Data	
Order product name	MASTER TL5 HE 21W/865 SLV/40
Full product name	MASTER TL5 HE 21W/865 SLV/40
Full product code	871150071011655
Order code	927926286555
Material Nr. (12NC)	927926286555


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500710116
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500867568

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 21W/865 SLV/40	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL5 HE 21W/865 SLV/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HE 21W/865 SLV/40



Life Expectancy Diagram - MASTER TL5 HE 21W/865 SLV/40

MASTER TL5 High Efficiency

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE 21W/865 SLV/40

