



MASTER TL5 High Output

MASTER TL5 HO 24W/830 UNP/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Product data

General Information		Color Rendering Index (Max)	
Cap-Base	G5 [G5]	Color Rendering Index (Min)	80
Life to 50% Failures Preheat (Nom)	30000 h	Color Rendering Index (Nom)	82
Features	na [Not Applicable]	LLMF 2000 h Rated	96 %
System Description	High Output	LLMF 4000 h Rated	95 %
LSF Preheat 2000 h Rated	99 %	LLMF 6000 h Rated	94 %
LSF Preheat 4000 h Rated	99 %	LLMF 8000 h Rated	93 %
LSF Preheat 6000 h Rated	99 %	LLMF 12000 h Rated	92 %
LSF Preheat 8000 h Rated	99 %	LLMF 16000 h Rated	91 %
LSF Preheat 16000 h Rated	97 %	LLMF 20000 h Rated	90 %
LSF Preheat 20000 h Rated	84 %		
Light Technical		Operating and Electrical	
Color Code	830 [CCT of 3000K]	Power (Nom)	22.5 W
Luminous Flux (Nom)	1950 lm	Lamp Current (Nom)	0.295 A
Luminous Flux (Rated) (Nom)	1700 lm		
Color Designation	Warm White (WW)	Temperature	
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	87 lm/W	Design Temperature (Nom)	35 °C
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	76 lm/W		

MASTER TL5 High Output

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	Green Plate
----------------------	-------------

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	25 kWh


Product Data

Full product code	871150063698055
-------------------	-----------------

Order product name	MASTER TL5 HO 24W/830 UNP/40
EAN/UPC - Product	8711500636980
Order code	927928083018
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927928083018
Net Weight (Piece)	52.000 g
ILCOS Code	FDH-24/30/1B-L/P-G5-16/550

Warnings and Safety

Dimensional drawing




Product


MASTER TL5 HO 24W/830 UNP/40

TL5 HO 24W/830

Photometric data




LDPB_TL5-HO8_830-Spectral power distribution B/W



LDPO_TL5-HO8_830-Spectral power distribution Colour


MASTER TL5 High Output

Lifetime



LDLE_TL5-HO8_0001-Life expectancy diagram

LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

