



MASTER TL5 High Output



MASTER TL5 HO 54W/840 UNP/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5
Features	na [Not Applicable]
Flux measurement reference	Sphere
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	4,500 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	80


Operating and Electrical	
Power Consumption	54.4 W
Lamp Current (Nom)	0.455 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	55 kWh
EPREL Registration Number	423563

MASTER TL5 High Output

Product Data	
Order product name	MASTER TL5 HO 54W/840 UNP/40
Full product name	MASTER TL5 HO 54W/840 UNP/40
Full product code	871150063740655
Order code	927929084018
Material Nr. (12NC)	927929084018


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500637406
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500637413

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 54W/840 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 54W/840 UNP/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HO 54W/840 UNP/40



Lumen Maintenance Diagram - MASTER TL5 HO 54W/840 UNP/40

MASTER TL5 High Output

Lifetime

Life Expectancy Diagram - MASTER TL5 HO 54W/840 UNP/40

