



MASTER PL-S 4 Pin



MASTER PL-S 9W/840/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2G7
Flux measurement reference	Sphere
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	570 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	73 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	8.8 W


Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	9 kWh
EPREL Registration Number	423594
Product Data	
Order product name	MASTER PL-S 9W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-S 9W/840/4P 1CT/5X10BOX
Full product code	871150026096370
Order code	26096370

MASTER PL-S 4 Pin

Material Nr. (12NC)	927936284011
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500260963
Numerator - Packs per outer box	50


EAN/UPC - Case	8711500260987
----------------	---------------

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 9W/840/4P 1CT/ 5X10BOX	28 mm	13 mm	128 mm	145 mm	151.1 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-S 9W/840/4P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-S 9W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-S 9W/840/4P 1CT/5X10BOX

MASTER PL-S 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-S 9W/840/4P 1CT/5X10BOX

