



MASTER PL-S 4 Pin

MASTER PL-S 11W/840/4P 1CT/10

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	2G7 [2G7]
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	900 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	11.6 W
Lamp Current (Nom)	0.160 A

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	13 kWh
Product Data	
Order product name	MASTER PL-S 11W/840/4P 1CT/10
Full product name	MASTER PL-S 11W/840/4P 1CT/10
Full product code	871869960692300
Order code	927936684065
Material Nr. (12NC)	927936684065
Local order code	MPLS11W8404P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699606923
Numerator - Packs per outer box	10

MASTER PL-S 4 Pin


EAN/UPC - Case	8718699606930
----------------	---------------

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 11W/840/4P 1CT/10	28 mm	13 mm	196 mm	214 mm	219.9 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-S 11W/840/4P 1CT/10

Lifetime



Life Expectancy Diagram - MASTER PL-S 11W/840/4P 1CT/10



Life Expectancy Diagram - MASTER PL-S 11W/840/4P 1CT/10

MASTER PL-S 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-S 11W/840/4P 1CT/10

